



PAR30/PAR20 LED

12.5PAR30L/F25 2700 DIM SO

Philips PAR30 and PAR20 LED Single Optic Lamps provide superior lighting aesthetics and optimal thermal efficiency in a sleek, lightweight design.


Product data

General Information		Temperature	
Cap-Base	E26 [Single Contact Medium Screw]	Lamp Current (Nom)	125 mA
Bulb Shape	PAR30L [PAR 3.75 inch/95mm Long]	Wattage Equivalent	75 W
Nominal Lifetime (Nom)	25000 h	Starting Time (Nom)	0.5 s
Switching Cycle	50000X	Warm Up Time To 60% Light (Max)	0.5 s
Technical Type	12.7-75W	Power Factor (Nom)	0.85
Light Technical		Voltage (Nom)	120 V
Color Code	827 [CCT of 2700K]	Controls and Dimming	
Beam Angle (Nom)	25 °	Dimmable	Yes
Initial lumen (Nom)	850 lm	Approval and Application	
Luminous Flux (Rated) (Nom)	850 lm	Suitable For Accent Lighting	Yes
Luminous Intensity (Nom)	4700 cd	Energy Efficiency Label (EEL)	Not applicable
Color Designation	Warm White (WW)	Product Data	
Rated Beam Angle	25 °	Order product name	120V PAR30L 12.7W 25D 2700K 900 D SO
Correlated Color Temperature (Nom)	2700 K	EAN/UPC - Product	046677454661
Luminous Efficacy (rated) (Nom)	67 lm/W	Order code	454660
Color Consistency	<6	Numerator - Quantity Per Pack	1
Color Rendering Index (Nom)	80	Numerator - Packs per outer box	6
LLMF At End Of Nominal Lifetime (Nom)	70 %	Material Nr. (12NC)	929001132304
Operating and Electrical			
Input Frequency	60 Hz		
Power (Rated) (Nom)	12.7 W		

PAR30/PAR20 LED

Net Weight (Piece)	0.001 kg
--------------------	----------

Dimensional drawing



PAR30L CL 120V 12.5W-75W 25D 2700K E26 D

Product	D	C
120V PAR30L 12.7W 25D 2700K 900 D SO	92 mm	116 mm

Photometric data

Accent Lighting - Spots

