



PAR38 LED

11PAR38/F25/830 ND 120V 6/1

Philips PAR38 LED Single Optic Lamps with AirFlux Technology improves shopping experience with superior lighting aesthetics and optimal thermal efficiency in a sleek, lightweight design.


Product data

General Information			
Cap-Base	E26 [Single Contact Medium Screw]	Power (Rated) (Nom)	11 W
Bulb Shape	PAR38 [PAR 4.75 inch/121mm]	Lamp Current (Nom)	170 mA
Nominal Lifetime (Nom)	10000 h	Wattage Equivalent	90 W
Switching Cycle	50000X	Starting Time (Nom)	0.5 s
Technical Type	11-90W	Warm Up Time To 60% Light (Nom)	0.5 s
		Power Factor (Nom)	0.5
		Voltage (Nom)	120 V
Light Technical		Temperature	
Color Code	830 [CCT of 3000K]	T-Case Maximum (Nom)	75 °C
Beam Angle (Nom)	25 °		
Initial lumen (Nom)	950 lm	Controls and Dimming	
Luminous Flux (Rated) (Nom)	950 lm	Dimmable	No
Luminous Intensity (Nom)	4085 cd		
Color Designation	White (WH)	Approval and Application	
Rated Beam Angle	25 °	Suitable For Accent Lighting	Yes
Correlated Color Temperature (Nom)	3000 K	Energy Efficiency Label (EEL)	Not applicable
Luminous Efficacy (rated) (Nom)	86 lm/W		
Color Consistency	<6	Product Data	
Color Rendering Index (Nom)	80	Order product name	120V PAR38 11W 25D 3000K ND
LLMF At End Of Nominal Lifetime (Nom)	70 %	EAN/UPC - Product	046677457990
Operating and Electrical		Order code	457993
Input Frequency	60 Hz	Numerator - Quantity Per Pack	1

PAR38 LED

Numerator - Packs per outer box	6
Material Nr. (12NC)	929001174766
Net Weight (Piece)	0.609 kg

Dimensional drawing



PAR38 120V 11W-90W 25D 3000K E26 ND

Product	D	C
---------	---	---

PAR38 LED

Photometric data

Accent Lighting - Spots

