



MasterColor CDM PAR38

MasterColor CDM 70/PAR38/FL/4K ALTO ELITE 12PK

Philips MasterColor® Ceramic Metal Halide PAR38 Lamps offer high-efficiency, ceramic metal halide reflector lamps with a stable color over lifetime and a crisp, sparkling light.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	Universal [Universal]
Life To 50% Failures (Nom)	16000 h
ANSI Code HID	C98/O
Light Technical	
Beam Angle (Max)	31 °
Beam Angle (Min)	19
Color Code	940 [CCT of 4000K]
Beam Angle (Nom)	25 °
Luminous Flux (Rated) (Nom)	4600 lm
Luminous Intensity (Nom)	15000 cd
Beam Description	Flood [Flood]
Color Designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	0.370
Chromaticity Coordinate Y (Nom)	0.372
Correlated Color Temperature (Nom)	4200 K
Color Rendering Index (Nom)	90

Operating and Electrical	
Power (Rated) (Nom)	70 W
Lamp Current (EM) (Nom)	0.8 A
Ignition Supply Voltage (Min)	235 V
Re-Ignition Time (Min) (Max)	8 min
Ignition Time (Max)	10 s
Voltage (Max)	120 V
Voltage (Min)	92 V
Voltage (Nom)	102 V
Controls and Dimming	
Dimmable	No
Run-Up Time 90% (Max)	2 min
Mechanical and Housing	
Bulb Finish	Clear (CL)
Luminaire Design Requirements	
Bulb Temperature (Max)	350 °C
Cap-Base Temperature (Max)	190 °C

MasterColor CDM PAR38


Product Data	
Order product name	MasterColor CDM 70/PAR38/FL/4K ALTO ELITE 12PK
EAN/UPC - Product	046677456498
Order code	456491
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	12
Material Nr. (12NC)	928493830901
Net Weight (Piece)	0.307 kg

Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)

Dimensional drawing



PAR 38

CDM 70W/940 E26 PAR38 FL 25D ALTO Elite

Product	D	D	C
MasterColor CDM 70/PAR38/FL/4K ALTO ELITE 12PK	4.76 in	121.0 mm	134.0 mm

