




Measurements:

<u>Height</u>	<u>Width</u>	<u>Extension</u>
15.25"	10.00"	8.00"
<u>BP Height</u>	<u>BP Width</u>	<u>HCO</u>
4.50"	4.50"	8.00000"
<u>Hanging Weight</u>		
2.20 lb		

Lamping:

Incandescent MB Incandescent	0 Rated Lumens
1.00 100W MB Incandescent	Color Temperature
100 total watt	
Dimmable : Standard Dimmer	

Shipping:

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
3.03 lb	11.42"	9.45"	11.42"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
1.0000	78320911295	Yes	

Finish:

Oriental Bronze OB

Material:

Aluminum

Certification:

Wet Location

Additional:

MB Incandescent (Not Included)