



**UPC Code :** 078477692400

**Country Of Origin :** China

## DSX12-70Z

Decora Rocker-Slide 1200VA-277VAC Fluorescent Dimmer for Mark 10 Ballasts, 60Hz, Single Pole or 3-Way - White, Ivory & Light Almond

Leviton Decora Rocker-Slide Mark 10® Powerline Fluorescent Ballast Dimmers provide smooth, slide-action, full-range dimming for Fluorescent loads. They combine a Decora rocker switch with a contemporary full-range slender slide bar for precise lighting control. With a new, streamlined style, Decora dimmers and fan speed control complement any interior design and are compatible with other Decora devices.

### Technical Information

#### Product Features

**Action :** Rocker Switch for ON/OFF, slide bar for lighting level control

**Available Colors :** Ivory-I Wht-W Gry-G Blk-E Brwn-B Light Almond-T, R-Red

**Color :** White, Ivory, Light Almond

**Frequency :** 60 Hz

**Load Rating :** 1200VA

**Load Type :** Electronic Mark 10 Powerline Fluorescent

**Ordering Notes :** Included White, Ivory and Light Almond Color Kit

**Preset :** Slide bar preserves desired lighting level

**Protection :** Radio/TV Filter

**Standards and Certifications :** cCSAus, NOM

**Style Name :** Decora

**Switch Type :** Single-Pole & 3-Way

**Type :** Dimmer

**Voltage :** 277 VAC

**Wallplate :** Order Separately

**Warranty :** 5-Year Limited

### Features and Benefits

- New aesthetically pleasing design with rocker switch and slender dimmer control slide bar
- Integrated linear full-range slide control for easy, precise operation
- Single pole or 3-way operation (when using 3-way switch); packaged with White, Ivory, and Light Almond color change kits
- Additional color change kits available in Black, Brown, Red and Gray
- Slim, compact housing fits easily into a standard wallbox and is suitable for multi-gang installations with other Decora products
- The slide bar location preserves the selected brightness level when the dimmer is switched OFF
- No fins for multi-gang installation
- Built-in radio/TV interference filter

### SPECIFICATION SUBMITTAL

<b>JOB NAME:</b> <input type="text"/> <b>JOB NUMBER:</b> <input type="text"/>	<b>CATALOG NUMBERS:</b> <input type="text"/> <input type="text"/> <input type="text"/> <input type="text"/>
---	---

**Leviton Manufacturing Co., Inc.**

201 North Service Road, Melville, NY 11747

Telephone: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday):  
+1-800-824-3005

**Leviton Manufacturing of Canada, Ltd.**

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·  
FAX: +1-800-824-3005 · [www.leviton.com/canada](http://www.leviton.com/canada)

**Leviton S. de R.L. de C.V.**

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-  
1797 · [www.leviton.com.mx](http://www.leviton.com.mx)

**Visit our Website at: [www.leviton.com](http://www.leviton.com)**

© 2018 Leviton Manufacturing Co., Inc. All Rights Reserved. Subject to change without notice.

**Leviton has a global presence.**

If you would like to know where your local Leviton office is located please go to:  
[www.leviton.com/international/contacts/](http://www.leviton.com/international/contacts/)

