

8 in. 3000K, 1500lm LED Downlight, (2x18W) or (1x32W) CFL Replacement, Non-Dimmable.

- Replaces CFL pin based lamps up to 36W (2x18W), (1x32W)
- Fits standard 8 in. CFL frame
- 120-277V input voltage
- 3000K, warm white light – ideal for most commercial, hospitality and residential applications
- 82 CRI and low-glare optics to produce higher quality light than fluorescent lamps
- Reduces energy consumption compared to CFL downlights
- 40,000 hour design lifetime (90,000 hour L70 lifetime)
- UL Classified
- 5-year limited warranty



Specifications

Lamp Type	8 in. Downlight 3000K, 1500lm
Part Number	98943
Model	D8-L1500-C30-V277-W
Dimmable	No
Voltage	120-277V
Wattage	24
Color Temperature	3000K
Lumen Output	1500 lm
Efficacy	62.5 lm/W
CRI	82
Beam Angle	90°
Operating Temperature	-40°C to 40°C
Socket	N/A
Design life	40,000 hours (90,000 hour L70 Lifetime)
CBCP	N/A
Dimensions(L x W x H)	9.69 x 9.69 x 4.56 in
Weight	680 g

Certifications:





8 in. 3000K, 1500lm LED Downlight, (2x18W) or (1x32W) CFL Replacement, Non-Dimmable.

Additional Images:



Diagrams:



Lighting Facts:

Lighting Facts Per Bulb Information concernant l'éclairage Pour une ampoule	
Brightness/Luminosité	1500 lumens
Estimated Yearly Energy Cost	\$2.89
Estimation Des Coûts Énergétiques Annuels	
Based on 3 hrs/day, 11¢/kWh Sur la base de 3 heures / jour, 11 ¢ / kWh Cost depends on rates and use Le coût dépend du tarif et de l'utilisation	
Life/Durée de vie	36.5 years/années
Based on 3 hrs/day Sur la base de 3 heures/jour	
Light Appearance/Degré de luminosité	
Warm/Chaud	Cool/Froid
3000 K	
Energy Used/Energie utilisée	24 watts