

Direct Replacement Linear Tube

LED 4' Glass Linear Tube 5000k Specifications




The ETi 20 watt 2200 lumen LED 4' Glass tubes offer exceptional performance for precision lighting applications. These 4' linear LED tubes are high quality replacements for fluorescent lamps. The lamps work with most Instant Start electronic ballasts. They are UL listed for use in damp locations and are RoHS compliant with no lead or mercury. Non-dimmable. Warranty period 5 years or 60 months. Suitable for installations from -13°F to 113°F.

KEY FEATURES & BENEFITS

- 20 watt Low Power and High Performance
- 2200 Lumens
- 83 CRI, 5000K
- Glass tube with shatter resistant sleeve
- UL-Damp and Dry Location
- Rated Lifetime: 50,000 hours
- Works with existing Ballast

LAMP DIMENSIONS



SKU# 54140261
Dimension A = 1.1"
Dimension B = 47.2"



*NSF Certification date code 2216D

This light source meets restrictions on hazardous substances.

This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. For FCC Part 15 user information, please see www.etiled.us

APPLICATION INFORMATION

Typical applications for the LED tubes include direct replacement of existing fluorescent lamps. Includes; homes, museums, galleries, shop windows, restaurants, meeting rooms and hotel / motel locations.



855-384-7754 www.etissl.com

LED 4' Glass Tube 5000k

LED 54140261

SPECIFICATION DATA

Project _____

Item Number _____

Prepared by _____ Date _____

ORDERING INFORMATION

Description	Watt-age	Base Type	Input Voltage (VAC)	Average Rated Life ¹	Typical Lumens ²	CCT ³	GRI ⁴	R9	Power Factor	DUV	90-270° Beam Angle	0-180° Spacing	90-270° Spacing
4' LED T8	20	G13	120-277V	50,000	2200	5000k	>83	7.8	≥0.98	0.001	180	1.26	1.4

¹ Hours lifetime with 70% lumen maintenance

² Thermally stable typical lumens (±10%)

³ Thermally stable CCT (±10%)

⁴ Color rendering index

SHIPPING INFORMATION

Model Number	Item UPC	Item Dimensions (H x L x W)	Item Weight (lbs)	Inner Pack Qty	Inner Carton Bar Code	Inner Carton Dimensions (H x L x W)	Inner Pack Weight (lbs)	Master Pack Qty	Master Carton Bar Code	Master Dimensions (H x L x W)	Master Pack Weight (lbs)
54140261	8494890 05508	1.4" x 49.5" x 1.4"	.57	N/A	N/A	N/A	N/A	15	50849489 005503	8" x 50.4" x 8"	15.7

LED lighting facts
A Program of the U.S. DOE

Light Output (Lumens) 2200
Watts 20
Lumens per Watt (Efficacy) 110

Color Accuracy
Color Rendering Index (CRI) 83


Light Color
Correlated Color Temperature (CCT) 5000 (Daylight)

2700K 3000K 4500K 6500K

All results are according to: IESNA LM-79-2008 - Approved Method for the Electrical and Photometric Testing of Solid State Lighting. The U.S. Department of Energy (DOE) verifies product test data and results.

Visit www.lightingfacts.com for the Label Reference Guide.

Registration Number: YN04 BE9 13Y (1/31/2015)
Model Number: 54140261 (XX: 61-70) (1 lamp/1ballast GHE 1x32T8/U/V PSM M/C)
Type: Lamp - Linear



**The Americas Headquarters
720 Corporate Woods Parkway
Vernon Hills, IL 60081**

855-384-7754