



Standard

STANDARD RLCS140TPWI

Available for many fluorescent lamp types sold today, including Preheat, Rapid Start, 2-pin CFL, Slimline, High Output, Very High Output and Circline. Magnetic ballasts can be used in any application where these lamps are used.

Product data

General Information	
Lamp Type	FC16T9
Number of Lamps	1 piece/unit
Lamp Footage	-
Ballast Type	Magnetic Fluorescent
Base Model	RLCS140TPW
Suitable For Outdoor Use	Yes
Automatic Restart	Yes
Operating and Electrical	
Input Voltage	120 V
Input Frequency	60 Hz
Total Harmonic Distortion USA	10 %
Ignition Method	Rapid Start
Crestfactor (Nom)	1.5
Ignition Time (Nom)	1 s
Ballast Factor (Nom)	0.5
Power Factor (Nom)	0.53
Input Current (Nom)	0.44 A
Input Power (Nom)	28 W
Rated Lamp Power	40 W

Wiring	
Wire Striplength	0.50/0.375 mm
Lamp Connection	Series
Wire Length by Color	See data sheet
Wire Gauge (Nom)	18AWG mm
Wire Type	Solid
Remote Wiring Configuration Allowed	Yes
Tandem Wiring Configuration Allowed	No
Through Wiring Configuration Allowed	No
Max Ballast-Lamp Distance Remote Wiring	30'
Max Ballast-Lamp Distance Tandem Wiring	-
Max Ballast-Lamp Distance Through Wiring	-

Mechanical and Housing	
Housing Material	Metal
Housing	R4
Housing Dimensions	6.5" x 1.94" x 1.38"


Approval and Application	
EMC Immunity Standard	FCC Non-Consumer
Approval Marks	CSA certificate UL certificate RoHS Compliant
Hum And Noise Level	A

Standard

UL Recognized	No
Product Data	
Order product name	STANDARD RLCS140TPWI
EAN/UPC - Product	781087081426
Order code	913700501081

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	913700501081
Net Weight (Piece)	0.921 kg

Dimensional drawing



Product	A1	A2	B1	C1
STANDARD RLCS140TPWI	6.5 in	6 in	1.94 in	1.38 in

MAG BALLAST (1) FC16T9 CIRCLINE 120V

