



# T&B®

## Rigid/IMC Conduit Fittings

T&B Catalog Number:

XJG88-TB

UPC Number:

78621088114

Status:

Active

Description:

3 Inch XJG Conduit Expansion Coupling with Internal Bonding Jumper, Body Malleable Iron Zinc Plated, Internal Bonding Jumper Tinned Copper Braid, Packing PTFE/Synthetic Fiber Material, 8 Inch Movement

### Features

No disassembly necessary to install. Fast, simple, and requires fewer steps.

True Internal Bonding Jumper-no external grounding strap required, tamper-proof internal jumper protected from the environment.

Exceeds code requirements for long conduit runs to permit linear movement.

### Application

Allows for the contraction and expansion of a conduit run without reducing the mechanical or bonding integrity of the raceway.

### General

Trade Size (inches)	3
Material	Malleable Iron
Finish	Zinc Plated

### Dimension Information

Dimension A (inches)	4.96
B-Length (inches)	16.12
C-Height (inches)	5.25
Movement (inches)	8

### Specifications

3dmodel	Available on Website
---------	----------------------

### Packaging

Package in Units	1
T&B Sold in UOM	Each
T&B Weight Per UOM	18.7 lbs. Each

### Application Support

T&B Instruction Sheets	ta02289-tb2
------------------------	-------------

### Certifications

RoHS Compliance	No
-----------------	----

### Certifications



File Nbr:

E 23018

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)