

Straight Blade Devices  
 20A, 125V, 2 Pole, 3 Wire Grounding  
 Commercial Specification Grade Duplex  
 Receptacles for Controlled Applicatoins

# HUBBELL

## Features

- Permanently marked with universal power symbol and the word "CONTROLLED" to visually identify receptacles used in automatic energy management systems
- Markings can be read regardless of mounting orientation
- Complies with NEC Section 406.3, ASHRAE 90.1, and California Title 24 requirements
- Complements Hubbell's Load Logic control's or any available energy management system

## Ordering Information

| Description                       | Device Color | UPC          | Catalog Number |
|-----------------------------------|--------------|--------------|----------------|
| Smooth face, back and side wired. | White        | 783585551555 | DR20C2WHI      |

## Listings


UL Listed to UL498 File No. E2186  
 CSA Certified 22.2, No. 42  
 Fed. Spec. W-C-596  
 NEMA® WD-6 Compliant

## Specifications

|                                 |                                    |
|---------------------------------|------------------------------------|
| Face                            | Nylon                              |
| Base                            | Nylon                              |
| Power Contacts                  | .030 in. (.8) Brass                |
| Ground Contacts                 | Brass                              |
| Wire Clamp                      | .062 in. (1.6) Nickel plated steel |
| Terminal Screws                 | Plated steel                       |
| Mounting Strap                  | .040 in. (1) Galvanized steel      |
| Automatic Self-grounding Staple | Stainless steel                    |
| Mounting Screws                 | Galvanized Steel                   |

## Performance

| Electrical              |  |
|-------------------------|--|
| Current Interrupting    | Certified for current interrupting at full rated current |
| Dielectric Voltage      | Withstands 2,000V minimum                                |
| Mechanical              |  |
| Product Identification  | Ratings are a permanent part of the device               |
| Terminal Accommodation  | #14-#10 AWG stranded or solid copper wire only           |
| Terminal Identification | Terminals identified in accordance with UL 498 and CSA   |
| Environmental           |  |
| Flammability            | UL 94 V-2  |
| Operating Temperatures  | Maximum continuous 75°C; minimum -40°C (w/o impact)      |



3 4  
 PAD PRINT  
 PER HPS #32A

## Online Resources

[eCatalog](#)

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

