



MR16/GU10/PAR16 LED

6.6MR16/F35/3000 DIM 12V

Philips MR16 Dimmable LED Lamps provide ambient level light to illuminate hard to maintain applications. Increased transformer compatibility allows for operation on a wider range of transformers. Available in dimmable and non-dimmable versions, these lamps are ideal for track and open recessed fixtures in retail, hospitality and residential spaces.

Product data


General Information		Luminous Flux In 90° Cone (Rated)	
Cap-Base	GU5.3 [GU5.3]		395 lm
Bulb Shape	MR16 [2inch/50mm]	Operating and Electrical	
Nominal Lifetime (Nom)	25000 h	Input Frequency	60 Hz
Switching Cycle	50000X	Power (Rated) (Nom)	6.6 W
Technical Type	6.6-35W	Lamp Current (Nom)	800 mA
Light Technical		Wattage Equivalent	35 W
Color Code	830 [CCT of 3000K]	Starting Time (Nom)	0.5 s
Beam Angle (Nom)	35 °	Warm Up Time To 60% Light (Nom)	0.5 s
Light Distribution	Medium beam 35°	Power Factor (Nom)	0.7
Initial lumen (Nom)	395 lm	Voltage (Nom)	12 V
Luminous Flux (Rated) (Nom)	395 lm	Temperature	
Luminous Intensity (Nom)	1000 cd	T-Case Maximum (Nom)	100 °C
Color Designation	White (WH)	Controls and Dimming	
Rated Beam Angle	35 °	Dimmable	Yes
Correlated Color Temperature (Nom)	3000 K	Approval and Application	
Luminous Efficacy (rated) (Nom)	64 lm/W	Suitable For Accent Lighting	Yes
Color Consistency	<6	Energy Efficiency Label (EEL)	Not applicable
Color Rendering Index (Nom)	80		
LLMF At End Of Nominal Lifetime (Nom)	70 %		

MR16/GU10/PAR16 LED

Energy Consumption kWh/1000 h	7 kWh
Product Data	
Order product name	6.6MR16/F35/3000 DIM 12V
EAN/UPC - Product	046677457600
Order code	457606

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001152204
Net Weight (Piece)	0.045 kg

Dimensional drawing



MR16 Black 12V 6.5-35W 36D 3000K D 25khr

Product	D	C
6.6MR16/F35/3000 DIM 12V	51 mm	51 mm

