



GE
Lighting

72113 - GE Ecolux® Mod-U-line® Starcoat® T8

F32T8SPX41U6/ECO

☞ Passes TCLP, which can lower disposal costs.

Product Photo



GENERAL CHARACTERISTICS

Base Description	Medium Bi-Pin
Base Face to Top of Lamp Max	22.250
Base Type	Pin/Plug-In
Mercury Content	3.75 mg
Mercury-Picogram per mean lm hr	76.1
Starting Temp (MIN) C-degrees	10 °C
Bulb Material	Soda lime
Rated Life Hours-nominal	20000 h
Primary Application	Full Wattage
Product Technology	Linear Fluorescent
Base	G13
Bulb Shape	T8

PHOTOMETRIC CHARACTERISTICS

Mean Lumens nominal	2465 lm
Nominal Initial Lumen per Watt	89
Initial Lumens-nominal	2800 lm
Color Rendering Index-CRI	82
Color Temperature	4100 K

PRODUCT INFORMATION

Product Code	72113
Description	F32T8SPX41U6/ECO
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168721134
Standard Package GTIN	10043168721131
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168721134

DIMENSIONS

Diameter	1.0 in
Bulb Diameter in Bend <Max>	1.13 in
Bulb Diameter in Bend <Min>	0.89 in
Bulb Diameter in Legs <Max>	1.1 in
Bulb Diameter in Legs <Min>	0.94 in
Lamplegs Center-Center Length	6.0 in
Nominal Length	22.5 in

ELECTRICAL CHARACTERISTICS

Current Crest Factor (MAX)	1.7
Cathode Resistance Ratio - Rh/Rc (MIN)	4.250
Cathode Resistance Ratio - Rh/Rc (MAX)	6.500
Rated power (Watts)	32 W

CAUTIONS & WARNINGS

Warning



Risk of Electric Shock


Turn power off before inspection
installation or removal.

Caution

Lamp may shatter and cause injury if broken

Wear safety glasses and gloves when handling lamp.
Do not use excessive force when installing lamp.





Jan 6, 2017 11:06:43 AM For additional information, visit www.gelighting.com