




LIGHTING
SCIENCE

LSPro

A19 9W Omnidirectional LED Lamp

EQUIVALENT TO 60W INCANDESCENT



Simple, powerful, flexible light that gives you illumination how and where you need it. This amazing little lamp gives you crisp clear light using only 9 watts of energy. Also, given it's omni-directional design you can count on maximum light in all the right areas.

- **Ominidirectional Light:** Approximately 220° beam angle gives you smooth, clean light
- **Uses Only 9W of Energy:** Save money and improve your energy efficiency with this low power consuming lamp that delivers big on light
- **Energy Star Rated:** A rating you can trust for quality



PRODUCT SPECIFICATIONS

SPECIFICATIONS ¹			
Color Temperature	2700K	3000K	5000K
Output (Lumens)	833	851	897
Power Factor	0.91	0.9	0.94
CRI	84	83	85
R9	14	9	18
Beam Angle	Omnidirectional		
Efficacy (LN/W)	96	98	102
Equivalent Source Standard	60		
Input Voltage (V)	120		
Power Consumption (W)	9		
Dimmable	Yes		
Operating Temperature Range (°F/°C)	-1 to +105 -18 to +40		
Product Dimensions (LxWxH in/cm)	3.17 x 3.17 x 5.2 8 x 8 x 11.2		
Weight (lbs/kg)	0.15 / 0.07		
Base	E26		
Packaging	4 Pack		
Lumen Maintenance	15,000		
Environmental Rating	Damp		
Certifications	UL, ES, FCC, RoHS		
Energy Star Rated	Yes		
Warranty	5 Years		

¹ Specifications and values supplied are nominal and are subject to change without notification

ORDERING INFORMATION

FAMILY	PRODUCT	WATTAGE EQUIVALENT	COLOR TEMPERATURE	VOLTAGE	PACKAGING
LSPRO	A19	60WE	W27 - Soft White (2700K)	120	4PK - Four Pack Box
			WW - Warm White (3000K)		
			CW - Daylight (5000K)		

example: LSPRO A19 60WE W27 120 4PK



LSPRO_A1960W_SpecSheet_RevB