

## 8 in. 3000K, 2000lm LED Downlight, (2x26W) or (1x42W) CFL Replacement, Non-Dimmable.

- Replaces CFL pin based lamps up to 52W (2x26W), (1x42W)
- Fits standard 8 in. CFL frames
- 120-277V input voltage
- 3000K, warm white light – ideal for most commercial, hospitality and residential applications
- 82 CRI and low-glare optics to produce higher quality light than fluorescent lamps
- Reduces energy consumption compared to CFL downlights
- 40,000 hour design lifetime (75,000 hour L70 lifetime)
- UL Classified
- 5-year limited warranty



Specifications	
Lamp Type	8 in. Downlight 3000K, 2000lm
Part Number	98944
Model	D8-L2000-C30-V277-W
Dimmable	No
Voltage	120-277V
Wattage	32
Color Temperature	3000K
Lumen Output	2000 lm
Efficacy	62.5 lm/W
CRI	82
Beam Angle	90°
Operating Temperature	-40°C to 40°C
Socket	N/A
Design life	40,000 hours (75,000 hour L70 Lifetime)
CBCP	N/A
Dimensions(L x W x H)	9.69 x 9.69 x 4.56 in
Weight	680 g

### Certifications:





# 8 in. 3000K, 2000lm LED Downlight, (2x26W) or (1x42W) CFL Replacement, Non-Dimmable.

## Additional Images:



## Diagrams:



## Lighting Facts:

Lighting Facts <small>Per Bulb</small>	
Information concernant l'éclairage <small>Pour une ampoule</small>	
<b>Brightness/Luminosité</b>	<b>800 lumens</b>
<b>Estimated Yearly Energy Cost</b>	<b>\$1.2</b>
<b>Estimation Des Coûts Énergétiques Annuels</b>	
<small>Based on 3 hrs/day, 11¢/kWh Sur la base de 3 heures / jour, 11 ¢ / kWh Cost depends on rates and use Le coût dépend du tarif et de l'utilisation</small>	
<b>Life/Durée de vie</b>	<b>22.8 years/années</b>
<small>Based on 3 hrs/day Sur la base de 3 heures/jour</small>	
<b>Light Appearance/Degré de luminosité</b>	
<small>Warm/Chaud      Cool/Froid</small>	
<b>Energy Used/Energie utilisée</b>	<b>10 watts</b>