


**MASONRY BOXES & PARTITIONS****Masonry Boxes, 3-1/2 in. Deep - Nongangable with Conduit KO's
5-Gang, 9-7/32 in. Wide****A58**

Catalog #: 699

APPLICATIONS

RACO[®] Masonry boxes are designed to accommodate the mounting of switches or other devices in masonry walls
2-1/2" deep boxes are used in 4" block walls, 3-1/2" deep boxes are used in 6" or 8" block walls

PRODUCT FEATURES

Rugged welded design does not fall apart during construction
Available from one to six gang configurations in both 2-1/2" and 3-1/2" depths
Rectangular shape fits square cuts in block
Large volume design allows for additional work room inside the box
Standard 1/2" and 3/4" concentric knockouts
Device ears inside the box prevent mortar from getting in the device holes
Steel voltage partition #971 fits all 2-1/2" or 3-1/2" depths
Standard wall plates can be used
N/A

UL LISTED

File E195978

COMPLIANCES

MSDS
www.hubbell-rtb.com/certifications/Hubbell-RACO_MSDS_for_Steel_Boxes_and_Covers.pdf

GENERAL PRODUCT INFORMATION

Wiring System: Conduit

CONFIGURATION

End Knockouts: 20 Conc.
Drawn or Welded: Welded
Gangs: 5
Side Knockout(s): 15 Conc.
Bottom Knockouts(s): 5 Conc.

DRAWING DIMENSIONS

Dimension A: 3-1/2 in.
Dimension B: 9-7/32 in.

PRODUCT MEASUREMENTS

Depth: 3-1/2 in.
Cubic Inches (cm³): 112.3 (1840.2)
Wt. Ea. (Lbs.): 2.230
Product Length (in.): 3.50
Product Width (in.): 3.75
Product Height (in.): 9.22

PACKAGING

Minimum Pack Qty.: 10
Std. Pkg.: 10
Product UPC-A Labeled: No
Weight (Lbs. Per/C): 223.00
Ship Carton Length (in.): 21.38
Ship Carton Width (in.): 7.50
Ship Carton Height (in.): 9.75
Ctn Weight (Lbs.): 22.30
Pallet Qty: 600
UPC Number: 050169006993
I2of5: 50050169006998