


NL-420 / NL-421
2" Pinhole with Baffle

TRIM DIMENSIONS



Trim OD: 5"
 Aperture: 1-7/8"
 Height: 1-7/8"

PRODUCT DESCRIPTION

The Pinhole with Baffle and deep regressed lamp position provides minimal aperture brightness. Excellent for concealing the light in commercial and residential applications.

FEATURES

Trim

Metal trim with 2" pinhole. Plastic baffle with deep grooves to reduce aperture glare. Gimbal ring allows lamp to be mounted on top of the trim.

Mounting

Trim includes three trim clips that securely mount trim in housing.

Compatible Housings

Compatible with Line Voltage and Low Voltage housings. See individual specification sheets for more information.

Lamp

Line Voltage (MR16 GU10)

50W 120V MR16 GU10 Max. (NSL-401AT/10; NSLIC-401AT/10; NSLR-404AT/10)

Line Voltage (PAR16)

45W PAR16 Max. (NS-401QAT; NSIC-401QAT; NSR-404QAT)

Low Voltage

20W-50W 12V MR16 (NL-401 Series; NL-402 Series; NLIC-401 Series; NLIC-402 Series; NLR-403 Series; NLR-404 Series; NLR-405 Series)

Labels and Listings

cULus Listed for Damp Location when used with compatible housing.

IMPORTANT:

DO NOT USE GLASS LENS WHEN ALREADY USING LAMP w/ GLASS COVER

2" Pinhole with Baffle

NL-420: White Metal Trim with 2" Pinhole and Black Baffle

NL-421: White Metal Trim with 2" Pinhole and White Baffle

Type
Project
Catalog No.
Lamp/Wattage

Compatible Housings

LINE VOLTAGE (MR16 GU10)			
Item Number	Installation Type	Lamp	Dimensions
NSL-401AT/10	Non-IC Air-Tight New Const.	50W MR16	W: 5-5/8" L: 8-1/2" H: 5-3/4"
NSLIC-401AT/10	IC Air-Tight New Construction	50W MR16	W: 8" L: 12-5/8" H: 8"
NSLR-404AT/10	Non-IC Air-Tight Remodel	50W MR16	W: 4-1/4" L: 11-1/4" H: 5-5/8"

LINE VOLTAGE (PAR16)			
Item Number	Installation Type	Lamp	Dimensions
NS-401QAT	Non-IC Air-Tight New Const.	45W PAR16	W: 5-5/8" L: 8-1/2" H: 5-3/4"
NSIC-401QAT	IC Air-Tight New Construction	45W PAR16	W: 5-1/4" L: 8-1/2" H: 6-3/8"
NSR-404QAT	Non-IC Air-Tight Remodel	45W PAR16	W: 4-1/4" L: 11-1/4" H: 5-5/8"

LOW VOLTAGE			
Item Number	Installation Type	Lamp	Dimensions
NL-401QAT/20	Non-IC AT New Const., Mag.	20W MR16	W: 6" L: 9" H: 5-1/2"
NL-401QAT/37	Non-IC AT New Const., Mag.	37W MR16	W: 6" L: 9" H: 5-1/2"
NL-401QAT	Non-IC AT New Const., Mag.	50W MR16	W: 6" L: 9" H: 5-1/2"
NL-401/50/277AT	Non-IC AT New Const., Mag.	50W MR16	W: 6" L: 9" H: 5-1/2"
NL-401AT/1EL	Non-IC AT New Const., Elec.	50W MR16	W: 6" L: 9" H: 5-1/2"
NL-401AT/2EL	Non-IC AT New Const., Elec.	50W MR16	W: 6" L: 9" H: 5-1/2"
NL-401/75	Non-IC AT New Const., Mag.	50W MR16	W: 7" L: 11-1/2" H: 6-3/8"
NL-401/75/277	Non-IC AT New Const., Mag.	50W MR16	W: 7" L: 11-1/2" H: 6-3/8"
NL-401/75/1EL	Non-IC AT New Const., Elec.	50W MR16	W: 7" L: 11-1/2" H: 6-3/8"
NL-401/75/2EL	Non-IC AT New Const., Elec.	50W MR16	W: 7" L: 11-1/2" H: 6-3/8"
NL-402S/20	Non-IC Shallow New Con., Mag.	20W MR16	W: 6" L: 8-1/2" H: 3-1/2"
NL-402S/37	Non-IC Shallow New Con., Mag.	37W MR16	W: 6" L: 8-1/2" H: 3-1/2"
NL-402S	Non-IC Shallow New Con., Mag.	50W MR16	W: 6" L: 8-1/2" H: 3-1/2"
NL-402S/1EL	Non-IC Shallow New Con., Elec.	50W MR16	W: 6" L: 8-1/2" H: 3-1/2"
NLIC-401QSAT/20	IC Air-Tight New Const., Mag.	20W MR16	W: 7-3/4" L: 12-1/2" H: 7-1/4"
NLIC-401QSAT/37	IC Air-Tight New Const., Mag.	37W MR16	W: 7-3/4" L: 12-1/2" H: 7-1/4"
NLIC-401QSAT	IC Air-Tight New Const., Mag.	50W MR16	W: 7-3/4" L: 12-1/2" H: 7-1/4"
NLIC-401AT/277V	IC Air-Tight New Const., Mag.	50W MR16	W: 10-3/4" L: 17-3/4" H: 7-1/2"
NLIC-401AT/1EL	IC Air-Tight New Const., Elec.	50W MR16	W: 7-3/4" L: 12-1/2" H: 7-1/4"
NLIC-401AT/2EL	IC Air-Tight New Const., Elec.	50W MR16	W: 7-3/4" L: 12-1/2" H: 7-1/4"
NLIC-402QSAT/20	IC Air-Tight Shallow NC, Mag.	20W MR16	W: 13-1/8" L: 14" H: 5-3/8"
NLIC-402QSAT/37	IC Air-Tight Shallow NC, Mag.	37W MR16	W: 13-1/8" L: 14" H: 5-3/8"
NLIC-402QSAT	IC Air-Tight Shallow NC, Mag.	50W MR16	W: 13-1/8" L: 14" H: 5-3/8"
NLIC-402AT/1EL	IC Air-Tight Shallow NC, Elec.	50W MR16	W: 13-1/8" L: 14" H: 5-3/8"
NLR-403S/20	Non-IC Shallow Remodel, Mag.	20W MR16	W: 4-7/8" L: 13-1/2" H: 3-1/2"
NLR-403S/37	Non-IC Shallow Remodel, Mag.	37W MR16	W: 4-7/8" L: 13-1/2" H: 3-1/2"
NLR-403S	Non-IC Shallow Remodel, Mag.	50W MR16	W: 4-7/8" L: 13-1/2" H: 3-1/2"
NLR-403S/1EL	Non-IC Shallow Remodel, Elec.	50W MR16	W: 4-7/8" L: 11-3/4" H: 3-1/2"
NLR-404QAT/20	Non-IC Air-Tight Remodel, Mag.	20W MR16	W: 4-7/8" L: 14-1/2" H: 5-5/8"
NLR-404QAT/37	Non-IC Air-Tight Remodel, Mag.	37W MR16	W: 4-7/8" L: 14-1/2" H: 5-5/8"
NLR-404QAT	Non-IC Air-Tight Remodel, Mag.	50W MR16	W: 4-7/8" L: 14-1/2" H: 5-5/8"
NLR-404/50/277	Non-IC Air-Tight Remodel, Mag.	50W MR16	W: 4-7/8" L: 14-1/2" H: 5-5/8"
NLR-404AT/1EL	Non-IC Air-Tight Remodel, Elec.	50W MR16	W: 4-7/8" L: 14-1/2" H: 5-5/8"
NLR-404AT/2EL	Non-IC Air-Tight Remodel, Elec.	50W MR16	W: 4-7/8" L: 14-1/2" H: 5-5/8"
NLR-404/75	Non-IC Remodel, Magnetic	50W MR16	W: 4-7/8" L: 14-1/2" H: 6-3/8"
NLR-404/75/277	Non-IC Remodel, Magnetic	50W MR16	W: 4-7/8" L: 14-1/2" H: 6-3/8"
NLR-404/75/1EL	Non-IC Remodel, Electronic	50W MR16	W: 4-7/8" L: 14-1/2" H: 6-3/8"
NLR-404/75/2EL	Non-IC Remodel, Electronic	50W MR16	W: 4-7/8" L: 14-1/2" H: 6-3/8"
NLR-405AT/20	Non-IC Air-Tight Remodel	20W MR16	W: 4-3/4" L: 4-3/4" H: 4-1/4"
NLR-405AT/37	Non-IC Air-Tight Remodel	37W MR16	W: 4-3/4" L: 4-3/4" H: 4-1/4"
NLR-405AT	Non-IC Air-Tight Remodel	50W MR16	W: 4-3/4" L: 4-3/4" H: 4-1/4"