

Integral Tube

LED

LED T8 U Bent Tube 4000K Specifications



The ETi 15 watt 1800 lumen LED T8 U Bent tube offers exceptional performance for precision lighting applications. These 6" Leg Spaced LED tubes are high quality replacements for fluorescent lamps and are available in 4000K. They are UL Classified for use in damp locations and are RoHS compliant with no lead or mercury. Non-dimmable. Warranty period 5 years or 60 months. Suitable for installations from -13°F to 113°F.


KEY FEATURES & BENEFITS

- 15 Watt
- 1800 Lumen Linear Tube
- 4000K
- UL E349551 - Classified
- Rated Lifetime: 50,000 Hours
- Easy, fast & safe installation
- Wire to one endcap



This light source meets restrictions on hazardous substances.

LAMP DIMENSIONS



SKU# 54293141
Dimension A = 7.09"
Dimension B = 22.5"

This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. For FCC Part 15 user information, please see www.etiled.us

APPLICATION INFORMATION

Typical applications for the LED tubes include retrofitting existing fluorescent fixtures. Includes; homes, museums, galleries, shop windows, restaurants, meeting rooms and hotel / motel locations.

ETi SOLID STATE™
LIGHTING
INC.

855-384-7754 www.etissl.com

LED T8 U Bent

LED

SPECIFICATION DATA

Project _____

Item Number _____

Prepared by _____ Date _____


ORDERING INFORMATION

Description	Watt- age	Base Type	Input Voltage (VAC)	Average Rated Life ¹	Typical Lumens ²	CCT ³	CRI ⁴	R9	Power Factor	DUV	90-270° Beam Angle	0-180° Spacing	90-270° Spacing
LED U Bent T8	15	G13	120- 277V	50,000	1800	4000k	83	26.3	≥0.9	.0015.	160	1.26	1.40
¹ Hours lifetime with 70% lumen maintenance													
² Thermally stable typical lumens (±10%)													
³ Thermally stable CCT (±10%)													
⁴ Color rendering index													

SHIPPING INFORMATION

Model Number	Item UPC	Item Dimensions (H x L x W)	Item Weight (lbs)	Inner Pack Qty	Inner Carton Bar Code	Inner Carton Dimensions (H x L x W)	Inner Pack Weight (lbs)	Master Pack Qty	Master Carton Bar Code	Master Dimen- sions (H x L x W)	Master Pack Weight (lbs)
54293141	8366070 09616	7.4" x 22.5" x 1.7"	.5	N/A	N/A	N/A	N/A	6	50836607 009611	24" x 8" x 8"	3.0

Integral LED Light Tube Wiring Diagram: Schéma de câblage intégral du tube à DEL : Diagrama de cableado del tubo de luz LED integral:



lighting facts®	
Light Output (Lumens)	1800
Watts	15
Lumens per Watt (Efficacy)	120
Color Accuracy (Color Rendering Index (CRI))	82
Light Color (Correlated Color Temperature (CCT))	4000 (Bright White)
Warm White	2700K
Bright White	4000K
Daylight	5000K

Minutely are according to IESNA LM-79-2000. Approved Reference for the Electrical and Photometric Testing of Solid State Lighting. The U.S. Department of Energy (DOE) verifies product life data and efficacy.

Visit www.lightingfacts.com for the Label Reference Guide.

Registration Number: 1588-150LED (Revised)

Model Number: 54293141-00

Type: Lamp: Linear

The Americas Headquarters
720 Corporate Woods Parkway
Vernon Hills, IL 60061

855-384-7754 www.etissl.com