




45 DEGREE CONDUIT AND CORD CONNECTORS - STEEL/MALLEABLE IRON

45 Degree Connectors Steel/Malleable Iron
N/A

B47.1



Catalog #: 3445

APPLICATIONS

For use in outdoor or indoor locations on flexible metallic liquidtight conduit and Type B flexible nonmetallic liquidtight conduit
Use to positively bond the conduit to a box or enclosure

PRODUCT FEATURES

RACO liquidtight connectors are suitable for use in Class I, Div. 2, Class II, Div. 1 & 2; and Class III, Div. 1 & 2 hazardous locations
Patented split gland-ring is designed to slip onto the conduit quickly gripping the jacket of the conduit, speeding installation, assuring a perfect seal, and preventing pullouts
All components are reusable - RACO liquidtight connectors may be easily disassembled and reused after years of service
Sealing washer (included) provides a liquidtight seal when terminating the connector in a threadless opening
Heavy duty locknut included with every RACO liquidtight connector assures continuity of ground
UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code, and packaged in pre-scored tear top cartons for an attractive presentation
All steel/iron components are zinc electro plated for added corrosion protection
3/8 in. to 2 in. Malleable iron bodies
3/8 in. to 1 in Steel nuts, 1-1/4 in. to 4 in. Malleable iron nuts
N/A

UL LISTED

Standard 514B, UL Listed E195969

CSA

C22.2 No. 18

GENERAL PRODUCT INFORMATION

Sub Class: Uninsulated
Trade Size: 1-1/4 in.

DRAWING DIMENSIONS

Dimension A: 2-3/16 in.
Dimension B: 23/32 in.
Thread Spec. B: 1-1/4 in. - 11-1/2 NPT
Dimension C: 1-13/16 in.
Dimension D: 1-1/2 in.

PACKAGING

Package Type: Carton
Ship Carton Qty.: 10
Product UPC-A Labeled: No
Weight (Lbs. Per/C): 95.50
Ship Carton Length (in.): 8.00
Ship Carton Width (in.): 7.13
Ship Carton Height (in.): 4.63
Ctn Weight (Lbs.): 9.55
UPC Number: 050169034453
I2of5: 50050169034458