



LINE VOLTAGE HIGH/LOW/OFF PIR FIXTURE INTEGRATED OUTDOOR PHOTO/MOTION SENSOR

FSP-211 | [Wattstopper](#)

FEATURES & BENEFITS

The FSP-211 mounts in an outdoor lighting fixture and provides multi-level control based on motion and/or daylight contribution. It controls 0-10VDC LED drivers or dimming ballasts, as well as non-dimming ballasts and, with an FSP-Lx Lens, is rated for wet and cold locations. All control parameters are adjustable via a wireless configuration tool capable of storing and transmitting sensor profiles.



- Fully adjustable high and low dimmed light levels; optional dusk to dawn control
- Designed for LED fixtures; rated for extreme temperatures and up to 200,000 on/off cycles
- Hold off setpoint with automatic calibration option for convenience and added energy savings
- Adjustable via handheld wireless configuration tool
- IP66 rated with choice of lenses for wet and outdoor locations, and mounting heights from 8' to 40'
- Adjustable time delay and cut off delay

SPECIFICATIONS

TECHNICAL INFO

Time Delay: 30 sec, 1 - 30 min, default 5 min

Cut Off Delay: disable, 1 - 60 min, 1 - 5 hrs

Photosensor Range: 1-250fc

GENERAL INFO

Typical Applications: Parking Facilities, Gas Stations, Pedestrian Pathways, Warehouses

Type: Fixture Integrated Outdoor Sensor

Special Features: IP66 rated

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

cULus: Yes

TECHNICAL INFORMATION

Volts: 120 - 277VAC, 50/60 Hz