



Measurements:

<u>Height</u>	<u>Width</u>	<u>Extension</u>
4.75"	18.00"	5.00"
<u>BP Height</u>	<u>BP Width</u>	
14.00"	4.00"	
<u>Hanging Weight</u>		
1.81 lb		

Lamping:

Incandescent MB	3,450 Rated Lumens
3.00 60W MB	Color Temperature
180 total watt	2,500 Rated Life
Dimmable : Standard	

Shipping:

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
1.95 lb	5.12"	2.56"	19.09"
<u>Master Pack Weight</u>	<u>Master Pack Width</u>	<u>Master Pack Height</u>	<u>Master Pack Length</u>
15.61 lb	10.63"	10.63"	19.29"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
8.0000	783209712324	Yes	

Finish:

Polished Chrome PC

Material:

Steel

Certification:

Damp Location
Location

Additional:

MB (Not Included)
Lighting Direction: Both