



# Core & Coil (71A) MH ~LT~ 175W

## CORE & COIL HID 71A5191001D

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

### Product data

General Information	
ANSI Code	M110
Lamp Type	50W MH
Number Of Lamps	1 piece/unit
Circuit Type	HX-HPF
Ballast Type	Magnetic HID
Base Model	71A5191
Core Size	3 X 4 (2 coil)
Suitable For Outdoor Use	Yes
Ignitor Catalog Number	LI533-H4
Ignitor Temperature Rating	105°C
Capacitor Value	6 MFD
Capacitor Catalog Number	7C060L30RA
Capacitor Requirements	280V
Capacitor Temperature Rating	105°C
Capacitor Diameter/Oval Dimensions	1.25 in
Capacitor Height	2.75 in
Automatic Restart	No

Operating and Electrical	
Input Voltage	120/208/240/277 V
Input Frequency	60 Hz
Power (Rated) (Nom)	50 W
Input Current (Open Circuit)	1.2/0.68/0.59/0.51 A
Input Current (Starting)	0.46/0.27/0.17/0.2 A
Input Current (Short Circuit)	0.42-0.65/0.25-0.37/0.21-0.32/0.16-0.27 A
Secondary Short Circuit Current	0.7-0.88 A
Constant Wattage Deviation	10%
Ballast Factor (Nom)	1
Power Factor (Nom)	0.90
Open Circuit Voltage	254 V
Input Current (Nom)	0.58/0.33/0.29/0.25 A A
Input Power (Nom)	67 W
Rated Lamp Power	50W W

Wiring	
Wire Striplength	0.5 mm
Wire Length By Color	12"
Wire Type	Stranded

## Core & Coil (71A) MH ~LT~ 175W

Remote Wiring Configuration Allowed	Yes
Max Ballast-Lamp Distance Remote Wiring	10'
Recommended Fuse Value	3/3/2/2 A

### Approval and Application


Open Circuit Voltage Test (Volts)	228-280 V
Approval Marks	ULR CSA certificate RoHS Compliant
Temperature Marking	A/A/A/A
UL Recognized	Yes
Hipot Test (1 Minute)	2000 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	H(180°C)

UL Temperature Code	1029A
---------------------	-------

### Product Data

Order product name	CORE & COIL HID 71A5191001D
EAN/UPC - Product	781087082782
Order code	913701135901
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	913701135901
Net Weight (Piece)	2.228 kg

### Dimensional drawing



Product	C1	C2	A1	A2	B1	B2
---------	----	----	----	----	----	----

MH BAL 50W M110 QUAD KIT

