


LED PARKING GARAGE FIXTURES
PKG SERIES



PKG30U50B & PKG45U50B



PRODUCT DESCRIPTION:

The surface mounted LED Parking Garage Canopy Luminaire is constructed with a shatter and UV resistant polycarbonate lens.

The LED modules use proprietary binning for color consistency. This fixture can be mounted to electrical boxes or directly to surfaces.

FEATURES:

- 30W replaces up to 150-175 Watt metal halide or 2 x 32W T8 fluorescent
- 45W replaces up to 175-250 Watt metal halide
- Self-contained driver
- Maintenance free and operates without UV
- Dusk-to-dawn and occupancy sensor compatible
- Can be mounted on electrical boxes or directly to surfaces
- LM-79/80 data available
- Does not attract insects

CONTROLS:

120VAC/208-277VAC Photocontrol: Voltage-specific photocontrols power the fixture when light levels reach 20 lux or below, and turn it off at 30 lux or higher. The operating temperature of the photocontrols are -30°F-120°F. Photocell mounted externally.

CONSTRUCTION:

Fixture: This rust- and corrosion-proof fixture is constructed of heavy duty cast aluminum one-piece housing, with a polyester powder coat. The fixture is sealed to be dirt and insect proof.

Lens: High quality shock proof polycarbonate lens with UV inhibitors.

LED Module: Copper plating provides high thermal transfer rate, minimizing junction temperature of LEDs to maximize service life.

MODEL SELECTION (Full list of order codes on pg. 2)		Typical order example: PKG45U50BPC27			
PKG			50		
FAMILY	WATTAGE (NOMINAL)	VOLTAGE	CCT	COLOR	OPTIONS
PKG= LED Parking Garage	30= 30W, replaces up to 150-175W MH 45= 45W, replaces up to 175-250W MH	U= 120-277V, std 3= 347V 4= 480V	50= 5000K	B= Bronze, std W= White	(OMIT)= None PC12= 120V Photocontrol PC27= 208-277V Photocontrol

SPECIFICATIONS:

ITEM	SPECIFICATION	PKG30U50B	PKG45U50B
		DETAILS	DETAILS
GENERAL PERFORMANCE	Input Power (W)	33	45
	Lumens Delivered (lm)	3290	4225
	Efficacy (lm/W)	101	95
	CRI	≥80	
	Lumen Maintenance (L70, TM-21 @ 25°C)	≥120,000	
	Color Temperature	5000K	
	Spacing Criteria	Available Upon Request	
	Color Consistency	Proprietary binning for uniform color	
ELECTRICAL	Power Factor (120V/277V)	≥0.99/≥0.95	
	Input Voltage	120-277V; 347/480V available	
PHYSICAL	Housing	Powder Coat Painted Aluminum	
	Lens	High-impact, UV-resistant Polycarbonate	
	Mounting	Fits electrical box or mount directly	
	Operating Temperature	-4°F to 122°F	
	Humidity	20-85% RH, non-condensing	
CERTIFICATION	Certification	cULus, LM-79, LM-80	
	Material Usage	RoHS compliant; no mercury	
	Environment	Outdoor, Wet location	
	Warranty	5 years	

Lighting layouts and spacing criteria available upon request

ORDERING*:

ORDER CODE	MODEL NUMBER	OPTIONS	FINISH	WATTAGE	VOLTAGE	CCT
76575	PKG30U50B	None	Bronze	35	120-277V	5000K
76582	PKG45U50B	None	Bronze	45		

*Please contact your MaxLite representative to order products that don't have order codes listed here.

DIMENSIONS:

