



Low-profile vandal-resistant fixture covers the footprint of most traditional canopy lights. Available in flat or drop lens with frosted and unfrosted options.

Color: White

Weight: 12.0 lbs

Project:

Type:

Prepared By:

Date:

Driver Info

Type: Constant Current
120V: 0.64A
208V: 0.40A
240V: 0.35A
277V: 0.30A
Input Watts: 63W
Efficiency: N/A

LED Info

Watts: 65W
Color Temp: 5000K (Cool)
Color Accuracy: 78 CRI
L70 Lifespan: 100000
Lumens: 7775
Efficacy: 123 LPW

Technical Specifications

Listings

UL Listing:

Suitable for Wet Locations. Covered Ceiling Mount Only.

DLC Listed:

This product is on the Design Lights Consortium (DLC) Qualified Products List and is eligible for rebates from DLC Member Utilities.

DLC Product Code: P2AJRY5Y

IESNA LM-79 & LM-80 Testing:

RAB LED luminaires and LED components have been tested by an independent laboratory in accordance with IESNA LM-79 and LM-80.

Electrical

Driver:

Class 2, 100-277V, 50-60Hz, 1650mA

THD:

6.1% at 120V, 10.1% at 277V

Construction

Maximum Ambient Temperature:

Suitable for use in 40°C (104°F) ambient temperatures

Cold Weather Starting:

Minimum starting temperature is -40°C (-40°F)

Housing:

Die-cast aluminum housing and lens frame with (4) 1/2" NPS side conduit entries and weatherproof rear wire plug and access plate

Mounting:

Ceiling mount to recessed junction with knockout template or directly to ceiling surface, utilizing side conduit entry points

IP Rating:

Ingress Protection rating of IP66 for dust and water

Lens:

Vandal-resistant polycarbonate textured opaque for low glare drop lens

Reflector:

Semi-specular, vacuum-metalized polycarbonate

Gaskets:

High-temperature silicone gaskets

Finish:

Our environmentally friendly polyester powder coatings are formulated for high-durability and long-lasting color

Green Technology:

Mercury and UV-free. RoHS compliant components. Polyester powder coat finish formulated without the use of VOCs or toxic heavy metals.

LED Characteristics

LEDs:

Discreet LEDs on PCB board

Color Stability:

RAB LEDs exceed industry standards for chromatic stability

Color Uniformity:

RAB's range of CCT (Correlated Color Temperature) follows the guidelines of the American National Standard for Specifications for the Chromaticity of Solid State Lighting (SSL) Products, ANSI C78.377-2017.

Other

Warranty:

RAB warrants that our LED products will be free from defects in materials and workmanship for a period of five (5) years from the date of delivery to the end user, including coverage of light output, color stability, driver performance and fixture finish. RAB's warranty is subject to all terms and conditions found at

Replacement:

Replaces up to 175W Metal Halide

Dimensions



Features

- Fits the footprint of older canopy lights
- Vandal resistant and UV resistant lens
- Ultra-high efficiency
- Clean, contemporary, low-profile design
- Available with drop lens or flat lens
- IP66 rated, keeps dust, bugs and water out
- Photo and motion sensor options available

Ordering Matrix

Family	Wattage	Color Temp	Lens	Motion Sensor & Finish	Driver Options	Photocell Options	Other Options
VANLED	65	Λ	Λ	W	Λ	Λ	Λ
75 = 75W	Blank = 5000K (Cool)	Blank = Drop lens	Blank = Bronze, no sensor	Blank = On/Off driver	Blank = No Option	USA = BAA Compliant	
65 = 65W	N = 4000K (Neutral)	F = Flat lens	W = White, no sensor	/D10 = 0-10V Dimming	/PCS = 120V Swivel	Blank = Standard	
52 = 52W	Y = 3000K (Warm)	FR = Frosted Drop Lens	MS = Bronze w/ SMS500 mini-sensor	/480 = 480V	/PCS2 = 277V Swivel		
40 = 40W		FFR = Frosted Flat Lens	MSW = White w/ SMS500 mini-sensor	/480/D10 = 480V w/ 0-10V dimming	/PCS4 = 480V Swivel		
20 = 20W							
10 = 10W							