

112-05460

HellermannTyton



Article Number: 112-05460

Description: Standard Cable Tie, 15.35" Long, 50lb Tensile Strength, PA66UV, Black, 100/pkg

Base Data	
Local Order Number	T50L0UVC2
Type	T50L
Color	Black (BK)
Features and Benefits	<ul style="list-style-type: none"> • UV stabilized cable ties contain an inhibitor which prolongs the life of the tie in UV exposures . • Inside serrations allow for strong hold on cables and wire bundles. • Head design provides high tensile strength with very low insertion force. • Bent tail ensures a quick and simple installation.
Quantity Per	pieces
Product Description	HellermannTyton standard cable ties feature inside serrations providing a positive hold onto wire and cable bundles. The head design guarantees high tensile strength, as well as a low insertion force. The bent tail design allows quick and simple installations by hand. For high volume applications, tensioning tools are available to ensure consistent and safe installation.
Short Description	Standard Cable Tie, 15.35" Long, 50lb Tensile Strength, PA66UV, Black, 100/pkg
Product Dimensions	
Minimum Tensile Strength (Imperial)	50.0lbs
Minimum Tensile Strength (Metric)	225.0N
Length L (Imperial)	15.35"
Length L (Metric)	390.0mm
Fixation Method	None
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.18"
Width W (Metric)	4.7mm
Bundle Diameter Min. (Imperial)	0.06"
Bundle Diameter Min. (Metric)	1.5mm

112-05460



Product Dimensions	Bundle Diameter Max. (Imperial)	4.3"
	Bundle Diameter Max. (Metric)	110.0mm
	Thickness T (Imperial)	0.05"
	Thickness T (Metric)	1.2mm
Material and Specifications		
	Material	Polyamide 6.6 UV-resistant (PA66UV)
	Material Shortcut	PA66UV
	US MILSPEC	MS3367-2-0
	Flammability	UL 94 V2
	Halogenfree	Yes
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
Certification/Specification	BACS38K	
Logistic and Packaging		
	Package Quantity (Metric)	100Pieces
	Customs Number(Schedule B)	3926909987
	Weight (Metric)	2.7kg