

SIMATIC HMI KTP400 COMFORT, COMFORT PANEL, TOUCH AND KEY OPERATION, 4" WIDESCREEN-TFT-DISPLAY, 16 MIL. COLORS, PROFINET INTERFACE, MPI/PROFIBUS DP INTERFACE, 4 MB USER MEMORY, WINDOWS CE 6.0, CONFIGURABLE FROM WINCC COMFORT V11



## General information

Product type designation	KTP400 Comfort
--------------------------	----------------

## Display

Design of display	TFT
Screen diagonal	4.3 in
Display width	95 mm
Display height	53.8 mm
Number of colors	16 777 216

## Resolution (pixels)

- |                               |           |
|-------------------------------|-----------|
| • Horizontal image resolution | 480 Pixel |
| • Vertical image resolution   | 272 Pixel |

## Backlighting

- |                                |              |
|--------------------------------|--------------|
| • MTBF backlighting (at 25 °C) | 80 000 h     |
| • Backlight dimmable           | Yes; 0-100 % |

## Control elements

### Keyboard fonts

- |                           |   |
|---------------------------|---|
| • Function keys           |   |
| — Number of function keys | 4 |

• Keys with LED	Yes
• System keys	No
• Numeric keyboard	Yes; Onscreen keyboard
• alphanumeric keyboard	Yes; Onscreen keyboard
<b>Touch operation</b>	
• Design as touch screen	Yes
<b>Expansions for operator control of the process</b>	
• DP direct LEDs (LEDs as S7 output I/O) — F1...Fx	4
• Direct keys (keys as S7 input I/O) — F1...Fx	4
• Direct keys (touch buttons as S7 input I/O)	32
<b>Installation type/mounting</b>	
Mounting position	vertical
Mounting in portrait format possible	Yes
Mounting in landscape format possible	Yes
maximum permissible angle of inclination without external ventilation	35°
<b>Supply voltage</b>	
Type of supply voltage	DC
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
<b>Input current</b>	
Current consumption (rated value)	0.13 A
Starting current inrush I <sup>2</sup> t	0.5 A <sup>2</sup> ·s
<b>Power</b>	
Active power input, typ.	3.1 W
<b>Processor</b>	
Processor type	ARM
<b>Memory</b>	
Flash	Yes
RAM	Yes
Memory available for user data	4 Mbyte
<b>Type of output</b>	
Info LED	No
Power LED	No
Error LED	No
Acoustics	
• Buzzer	Yes

- Speaker

No

## Time of day

### Clock

- |                              |   |
|------------------------------|---|
| • Hardware clock (real-time) | Yes                                     |
| • Software clock             | Yes                                     |
| • retentive                  | Yes; Back-up duration typically 6 weeks |
| • synchronizable             | Yes                                     |

## Interfaces

Number of industrial Ethernet interfaces	1
Number of RS 485 interfaces	1; RS 422/485 combined
Number of RS 422 interfaces	1
Number of RS 232 interfaces	0
Number of USB interfaces	1; USB 2.0
• USB Mini B	1; 5-pole
Number of 20 mA interfaces (TTY)	0
Number of parallel interfaces	0
Number of other interfaces	0
Number of SD card slots	2
With software interfaces	No

### Industrial Ethernet

- |  |                         |
|--|-------------------------|
| • Industrial Ethernet status LED           | 2                       |
| • Number of ports of the integrated switch | 1; No switch integrated |

## Protocols

PROFINET	Yes
Supports protocol for PROFINET IO	Yes
IRT	No
MRP	No
PROFIBUS	Yes
MPI	Yes

### Protocols (Ethernet)

- |          |     |
|----------|-----|
| • TCP/IP | Yes |
| • DHCP   | Yes |
| • SNMP   | Yes |
| • DCP    | Yes |
| • LLDP   | Yes |

### WEB characteristics

- |         |     |
|---------|-----|
| • HTTP  | Yes |
| • HTTPS | No  |
| • HTML  | Yes |
| • XML   | No  |
| • CSS   | Yes |

• Active X	No
• JavaScript	Yes
• Java VM	No
<b>Further protocols</b>	
• CAN	No
• EtherNet/IP	Yes
• MODBUS	Yes
<b>EMC</b>	
<b>Emission of radio interference acc. to EN 55 011</b>	
• Limit class A, for use in industrial areas	Yes
• Limit class B, for use in residential areas	No
<b>Degree and class of protection</b>	
IP (at the front)	IP65
Enclosure Type 4 at the front	Yes
Enclosure Type 4x at the front	Yes
IP (rear)	IP20
<b>Standards, approvals, certificates</b>	
CE mark	Yes
cULus	Yes
RCM (formerly C-TICK)	Yes
KC approval	Yes
<b>Marine approval</b>	
• Germanischer Lloyd (GL)	Yes
• American Bureau of Shipping (ABS)	Yes
• Bureau Veritas (BV)	Yes
• Det Norske Veritas (DNV)	Yes
• Lloyds Register of Shipping (LRS)	Yes
• Nippon Kaiji Kyokai (Class NK)	Yes
• Polski Rejestr Statkow (PRS)	No
<b>Use in hazardous areas</b>	
• ATEX Zone 2	Yes
• ATEX Zone 22	Yes
• IECEx Zone 2	Yes
• IECEx Zone 22	Yes
• cULus Class I Zone 1	No
• cULus Class I Zone 2, Division 2	Yes
• FM Class I Division 2	Yes
<b>Ambient conditions</b>	
<b>Ambient temperature during operation</b>	
• Operation (vertical installation)	

— For vertical installation, min.	0 °C
— For vertical installation, max.	50 °C
• Operation (max. tilt angle)	
— At maximum tilt angle, min.	0 °C
— At maximum tilt angle, min.	40 °C
• Operation (vertical installation, portrait format)	
— For vertical installation, min.	0 °C
— For vertical installation, max.	40 °C
• Operation (max. tilt angle, portrait format)	
— At maximum tilt angle, min.	0 °C
— At maximum tilt angle, min.	35 °C
<b>Ambient temperature during storage/transportation</b>	
• min.	-20 °C
• max.	60 °C
<b>Relative humidity</b>	
• Operation, max.	90 %; no condensation
<b>Operating systems</b>	
proprietary	No
<b>pre-installed operating system</b>	
• Windows CE	Yes
<b>Configuration</b>	
Message indicator	Yes
Alarm system (incl. buffer and acknowledgment)	Yes
Process value display (output)	Yes
Process value default (input) possible	Yes
Recipe management	Yes
<b>Configuration software</b>	
• STEP 7 Basic (TIA Portal)	No
• STEP 7 Professional (TIA Portal)	No
• WinCC flexible Compact	No
• WinCC flexible Standard	No
• WinCC flexible Advanced	No
• WinCC Basic (TIA Portal)	No
• WinCC Comfort (TIA Portal)	Yes; from V11
• WinCC Advanced (TIA Portal)	Yes; from V11
• WinCC Professional (TIA Portal)	Yes; from V11
<b>Languages</b>	
<b>Online languages</b>	
• Number of online/runtime languages	32
<b>Project languages</b>	
• Languages per project	32

## Functionality under WinCC (TIA Portal)

Libraries	Yes
Applications/options	
• Web browser	Yes
• Pocket Word	Yes
• Pocket Excel	Yes
• PDF Viewer	Yes
• Media Player	Yes
• SIMATIC WinCC Sm@rtServer	Yes
• SIMATIC WinCC Audit	Yes
Number of Visual Basic Scripts	Yes
Task planner	
• time-controlled	Yes
• task-controlled	Yes
Help system	
• Number of characters per info text	70
<b>Message system</b>	
• Number of alarm classes	32
• Bit messages	
— Number of bit messages	2 000
• Analog messages	
— Number of analog messages	50
• S7 alarm number procedure	Yes
• System messages HMI	Yes
• System messages, other (SIMATIC S7, Sinumerik, Simotion, etc.)	Yes
• Number of characters per message	80
• Number of process values per message	8
• Acknowledgment groups	Yes
• Message indicator	Yes
• Message buffer	
— Number of entries	256
— Circulating buffer	Yes
— retentive	Yes
— maintenance-free	Yes
<b>Recipe management</b>	
• Number of recipes	100
• Data records per recipe	200
• Entries per data record	200
• Size of internal recipe memory	512 kbyte
• Recipe memory expandable	Yes

Variables	
• Number of variables per device	1 024
• Number of variables per screen	50
• Limit values	Yes
• Multiplexing	Yes
• Structures	Yes
• Arrays	Yes
Images	
• Number of configurable images	500
• Permanent window/default	Yes
• Global image	Yes
• Pop-up images	Yes
• Slide-in images	Yes
• Image selection by PLC	Yes
• Image number in the PLC	Yes
Image objects	
• Number of objects per image	50
• Text fields	Yes
• I/O fields	Yes
• Graphic I/O fields (graphics list)	Yes
• Symbolic I/O fields (text list)	Yes
• Date/time fields	Yes
• Switches	Yes
• Buttons	Yes
• Graphic display	Yes
• Icons	Yes
• Geometric objects	Yes
Complex image objects	
• Number of complex objects per screen	5
• Alarm view	Yes
• Trend view	Yes
• User view	Yes
• Status/control	Yes
• Sm@rtClient view	Yes
• Recipe view	Yes
• f(x) trend view	Yes
• System diagnostics view	Yes
• Media Player	Yes
• HTML browser	No
• PDF display	Yes
• IP camera display	Yes

• Bar graphs	Yes
• Sliders	Yes
• Pointer instruments	Yes
• Analog/digital clock	Yes
<b>Lists</b>	
• Number of text lists per project	300
• Number of entries per text list	30
• Number of graphics lists per project	100
• Number of entries per graphics list	30
<b>Archiving</b>	
• Number of archives per device	10
• Number of entries per archive	10 000
• Message archive	Yes
• Process value archive	Yes
• Archiving methods	
— Sequential archive	Yes
— Short-term archive	Yes
• Memory location	
— Memory card	Yes
— USB memory	Yes
— Ethernet	Yes
• Data storage format	
— CSV	Yes
— TXT	Yes
— RDB	Yes
<b>Security</b>	
• Number of user groups	50
• Number of user rights	32
• Number of users	50
• Password export/import	Yes
• SIMATIC Logon	Yes
<b>Logging through printer</b>	
• Alarms	Yes
• Report (shift log)	Yes
• Hardcopy	Yes
• Electronic print to file	Yes; PDF, HTML
<b>Character sets</b>	
• Keyboard fonts	
— US English	Yes
<b>Transfer (upload/download)</b>	
• MPI/PROFIBUS DP	Yes



• USB	Yes
• Ethernet	Yes
• using external storage medium	Yes
<b>Process coupling</b>	
• S7-1200	Yes
• S7-1500	Yes
• S7-200	Yes
• S7-300/400	Yes
• LOGO!	Yes
• WinAC	Yes
• SINUMERIK	Yes; with SINUMERIK option package
• SIMOTION	Yes
• Allen Bradley (EtherNet/IP)	Yes
• Allen Bradley (DF1)	Yes
• Mitsubishi (MC TCP/IP)	Yes
• Mitsubishi (FX)	Yes
• OMRON (FINS TCP)	No
• OMRON (LINK/Multilink)	Yes
• Modicon (Modbus TCP/IP)	Yes
• Modicon (Modbus)	Yes
• OPC UA Client	Yes
• OPC UA Server	Yes
<b>Service tools/configuration aids</b>	
• Backup/Restore manually	Yes
• Backup/Restore automatically	Yes
• Simulation	Yes
• Device switchover	Yes
<b>Peripherals/Options</b>	
<b>Peripherals</b>	
• Printer	Yes
• SIMATIC HMI MM memory card: Multi Media Card	Yes; Up to 128 MB
• SIMATIC HMI SD memory card: Secure Digital memory card	Yes; Up to 2 GB
• SIMATIC HMI CF memory card Compact Flash Card	No
• USB memory	Yes
• SIMATIC IPC USB Flashdrive (USB stick)	Yes; Up to 16 GB
• SIMATIC HMI USB stick	Yes; Up to 8 GB
• Network camera	Yes
<b>Mechanics/material</b>	

Enclosure material (front)	
• Plastic	Yes
• Aluminum	No
• Stainless steel	No

### Dimensions

Width of the housing front	140 mm
Height of housing front	116 mm
Mounting cutout, width	123 mm
Mounting cutout, height	99 mm
Overall depth	49 mm

### Weights

Weight without packaging	0.6 kg
Weight incl. packaging	0.7 kg

**last modified:** 10/26/2017