

— Telegram length, max.	1 kbyte
— Bits per character	7 or 8
— Number of stop bits	1 (Standard), 2
— Parity	No parity (standard); even, uneven, mark (parity bit always 1); space (parity bit always 0)
3964 (R)	
— Telegram length, max.	1 kbyte
— Bits per character	7 or 8
— Number of stop bits	1 (Standard), 2
— Parity	No parity (standard); even, uneven, mark (parity bit always 1); space (parity bit always 0)
Modbus RTU master	
— Address area	1 through 49 999 (Standard Modbus addressing)
— Number of slaves, max.	247; slave numbers 1 through 247, per MODBUS network segment maximum 32 devices, additional repeaters needed to expand the network to maximum configuration
MODBUS RTU slave	
— Address area	1 through 49 999 (Standard Modbus addressing)
Interrupts/diagnostics/status information	
Diagnostic functions	Yes
Degree and class of protection	
Degree of protection acc. to EN 60529	
• IP20	Yes
Standards, approvals, certificates	
CE mark	Yes
cULus	Yes
FM approval	Yes
RCM (formerly C-TICK)	Yes
KC approval	Yes
Ambient conditions	
Free fall	
• Fall height, max.	0.3 m; five times, in product package
Ambient temperature during operation	
• permissible temperature range	-20 °C to +60 °C horizontal mounting, -20 °C to 50 °C vertical mounting, 95% humidity, non-condensing
• permissible temperature change	5°C to 55°C, 3°C / minute
Ambient temperature during storage/transportation	
• min.	-40 °C
• max.	70 °C
Air pressure acc. to IEC 60068-2-13	
• Operation, min.	795 hPa

- Operation, max. 1 080 hPa
- Storage/transport, min. 660 hPa
- Storage/transport, max. 1 080 hPa

Relative humidity

- permissible range (without condensation) at 25 °C 95 %

Mechanics/material

Enclosure material (front)

- Plastic Yes

Dimensions

Width	38 mm
Height	62 mm
Depth	21 mm

Weights

Weight, approx. 40 g

last modified: 03/24/2017