

SIMATIC S7-300, DIGITAL INPUT SM 321, OPTICALLY ISOLATED,
16DI, 24 V DC, 1 X 20 PIN



Figure similar

Supply voltage	
Load voltage L+	
• Rated value (DC)	24 V
• permissible range, lower limit (DC)	20.4 V
• permissible range, upper limit (DC)	28.8 V
Input current	
from backplane bus 5 V DC, max.	10 mA
Power loss	
Power loss, typ.	3.5 W
Digital inputs	
Number of digital inputs	16
Input characteristic curve in accordance with IEC 61131, type 1	Yes
Number of simultaneously controllable inputs	
horizontal installation	
— up to 40 °C, max.	16

— up to 60 °C, max.	16
vertical installation	
— up to 40 °C, max.	16
Input voltage	
• Type of input voltage	DC
• Rated value (DC)	24 V
• for signal "0"	-30 to +5V
• for signal "1"	13 to 30V
Input current	
• for signal "1", typ.	7 mA
Input delay (for rated value of input voltage)	
for standard inputs	
— parameterizable	No
— at "0" to "1", min.	1.2 ms
— at "0" to "1", max.	4.8 ms
— at "1" to "0", min.	1.2 ms
— at "1" to "0", max.	4.8 ms
Cable length	
• shielded, max.	1 000 m
• unshielded, max.	600 m
Encoder	
Connectable encoders	
• 2-wire sensor	Yes
— permissible quiescent current (2-wire sensor), max.	1.5 mA
Isochronous mode	
Isochronous operation (application synchronized up to terminal)	No
Interrupts/diagnostics/status information	
Diagnostic functions	No
Alarms	
• Diagnostic alarm	No
• Hardware interrupt	No
Diagnostics indication LED	
• Status indicator digital input (green)	Yes
Potential separation	
Potential separation digital inputs	
• between the channels	No
• between the channels, in groups of	16
• between the channels and backplane bus	Yes; Optocoupler

Isolation	
Isolation tested with	500 V DC
Connection method	
required front connector	20-pin
Dimensions	
Width	40 mm
Height	125 mm
Depth	120 mm
Weights	
Weight, approx.	200 g
last modified:	03/24/2017