



# Energy Saver Reflectors

## EL/A PAR38 23W 2PC 4/1

Looking for an energy saver that doesn't look like one? The Philips EnergySaver family provides energy efficient lighting options that don't just provide similar light as your standard incandescent light bulb, they also have the same classic shapes. Philips Energy Saver reflector flood compact fluorescents reduce operating costs without sacrificing light quality compared to incandescent equivalents. With dimmable and hard glass options, they are ideal for recessed and track lighting indoors and outdoors.


### Product data

General Information	
Cap-Base	E26 [ Single Contact Medium Screw]
Bulb Shape	PAR38 2 Pieces
Life With 3 Hour Per Day Use	9.1 a
Light Technical	
Color Code	827 [ CCT of 2700K]
Luminous Flux (Nom)	1300 lm
Luminous Intensity (Nom)	420 cd
Color Designation	Warm White (WW)
Lumen Maintenance 2000 h (Nom)	80 %
Lumen Maintenance 5000 h (Nom)	70 %
Chromaticity Coordinate X (Nom)	463
Chromaticity Coordinate Y (Nom)	420
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	56 lm/W
Color Rendering Index (Min)	81
Operating and Electrical	
Input Frequency	50 or 60 Hz

Power (Rated) (Nom)	23 W
Lamp Current (Nom)	330 mA
Power Factor (Nom)	0.55
Voltage (Nom)	110-127 V
Approval and Application	
Estimated Energy Cost Per Year	2.77 \$
Product Data	
Order product name	EL/A PAR38 23W 2PC 4/1
EAN/UPC - Product	046677227913
Order code	929689721102
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	929689721102
Net Weight (Piece)	0.338 kg

Energy Saver Reflectors

Dimensional drawing



PAR38 Refl 23W/827 E26 110-127V 2P

Product	D	C	F
EL/A PAR38 23W 2PC 4/1	122 mm	137 mm	43.5 mm

