



PAR38 LED

32PAR38/LED/830/F25/ND SO 120V 6/1

Philips PAR38 LED Single Optic Lamps with AirFlux Technology improves shopping experience with superior lighting aesthetics and optimal thermal efficiency in a sleek, lightweight design.

Product data


General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Bulb Shape	PAR38 [PAR 4.75 inch/121mm]
Nominal Lifetime (Nom)	25000 h
Switching Cycle	50000X
Technical Type	32-250W
Light Technical	
Color Code	830 [CCT of 3000K]
Beam Angle (Nom)	25 °
Initial lumen (Nom)	2800 lm
Luminous Flux (Rated) (Nom)	2800 lm
Luminous Intensity (Nom)	8000 cd
Color Designation	White (WH)
Rated Beam Angle	25 °
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	88 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz

Power (Rated) (Nom)	32 W
Lamp Current (Nom)	280 mA
Wattage Equivalent	250 W
Starting Time (Nom)	0.5 s
Warm Up Time To 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.85
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	95 °C
Controls and Dimming	
Dimmable	No
Approval and Application	
Suitable For Accent Lighting	Yes
Energy Efficiency Label (EEL)	Not applicable
Product Data	
Order product name	120V PAR38 32W 25D 3000K SO
EAN/UPC - Product	046677460525
Order code	460527
Numerator - Quantity Per Pack	1

PAR38 LED

Numerator - Packs per outer box	6
Material Nr. (12NC)	929001202404
Net Weight (Piece)	0.540 kg

Dimensional drawing



PAR38 35W-70W 2800lm 25D 3000K E26 ND

Product	D	C
120V PAR38 32W 25D 3000K SO	122 mm	133 mm

PAR38 LED

Photometric data

Accent Lighting - Spots

