



F54T5HO/850	
Std. Pack Qty.	40
Order Code	

PRODUCT SPECIFICATION

FLUORESCENT LAMPS



**GENERAL CHARACTERISTICS**

Lamp Type	Linear
Bulb	T5
Base	G5
Watts	54
Rated Avg. Life (hrs)	
3 hours per start	30,000
12 hours per start	36,000

**DIMENSIONS**

Norminal Overall Length (inches) (C)	45.80
Norminal Bulb Diameter (inches) (D)	0.63
Face to End of Opposing End (inches)	
Max. (B)	45.52
Min. (B)	45.42

**Spectral Power Distribution**



**PHOTOMETRIC CHARACTERISTICS**

Initial Lumens	5100
Mean Lumens	4650
Color Temperature	5000 K
Color Rendering Index (CRI)	82


**ELECTRICAL CHARACTERISTICS**

Min. Starting Temperature (C)	-20
Min. Cathode Resistance Ratio (Rh/Rc)	4.25
Max. Cathode Resistance Ratio (Rh/Rc)	6.5
Max. Current Crest Factor	1.7

**Features**

- 

**Lamp Mortality**



**Lumen Maintenance**

