

HITACHI

Inspire the Next

Product Highlights

- REACH & RoHS 2 compliant.
- Made in USA.
- UL Verified.
- Low Smoke Plenum construction.
- Guaranteed minimum performance.
- Enhanced performance beyond TIA Standard.
- Tested from 1 to 555 MHz.

TIA PARAMETER	GUARANTEED HEADROOM
NEXT loss	+3 dB
PSNEXT loss	+3 dB
ACRF	+3 dB
PSACRF	+3 dB

- Supports up to 100 watts of power.

Packaging

- 1,000 foot (305m) reels
- 1,000 foot (305m) Reelex (featuring reverse sequential numbering)

Options

- CMP-50 rated cables available

Applications

- Including:
 - HDBase-T
 - 10G BASE-T 10 Gigabit Ethernet (limited distance)
 - 1000 BASE-T Gigabit Ethernet
 - 1000 Mbps ATM
 - 622 Mbps ATM
 - 100 BASE-T Ethernet
 - Broadband Video
 - POE
 - POE+

Temp Range

- Storage Temperature
 - 40C to +60C (-40F to +140F)
- Installation Temperature
 - 0C to +60C (+32F to +140F)
- Operation Temperature
 - 20C to +75C (-4F to +167F)

Plus™ (Plenum)

(c(UL)us Listed Type CMP, CSA Type FT6)

HITACHI PART NO.	NO. OF PAIRS	CALCULATED CABLE O.D. in.	mm	CABLE WEIGHT lbs/1000ft	kg/305m
30025-8-XXY	4	.20	5.1	25.74	11.67

Plus™ (Riser)

(c(UL)us Listed Type CMR, CSA Type FT4)

HITACHI PART NO.	NO. OF PAIRS	CALCULATED CABLE O.D. in.	mm	CABLE WEIGHT lbs/1000ft	kg/305m
30024-8-XXY	4	.23	5.84	22.87	10.37

Building a Part Number

Base Part Number Ex.	No. of Conductors	Jacket Color	Reel Type
30025	8	XX	Y


Jacket Colors (XX):

Black(BK); Blue(BL); Brown(BR); Gray(GA); Green(GR); Red(RD); White(WH); Yellow(YE)

Reel Type (Y):

Reelex Boxes(2); Reels(3)

Features



DIELECTRIC MATERIALS	RISER	PLENUM
Primary Insulation	Polyolefin	Plenum-rated fluoropolymer
Overall Jacket	Flame-retardant thermoplastic	Low-smoke, flame-retardant thermoplastic
Filler	Flame-retardant thermoplastic	Plenum-rated polymer

Hitachi Cable America reserves the right to revise any specifications.

Electrical Characteristics

Input Impedance	100 ± 15Ω (1.0 to 250 MHz)
Maximum conductor resistance	9.38 Ω/100 meters @ 20C
Maximum resistance unbalance	5%
Maximum capacitance unbalance	330 pF/100 meters
Maximum delay skew	45 ns/100 meters
Nominal velocity of propagation (NVP)	riser, 68% plenum, 70%
Voltage Rating	300 Volts
Ampacity ¹	.5 Amps/conductor



Photo is for representation purposes only.

Transmission Specifications

ANSI/TIA 568-C.2 Category 6 Verified

ISO/IEC 11801, 2nd ed. Class E Compliant

Freq. (MHz)	Ins. Loss		NEXT		PSNEXT		ACR		PSACR		ACRF		PSACRF		Return Loss	
	Std.	Max.	Std.	Min.	Std.	Min.	Cal.	Min.	Cal.	Min.	Std.	Min.	Std.	Min.	Std.	Min.
1	2.0	2.0	74.3	77.3	72.3	75.3	72.3	75.3	70.3	73.3	67.8	70.8	64.8	67.8	20.0	20.0
4	3.8	3.8	65.3	68.3	63.3	66.3	61.5	64.5	59.5	62.5	55.8	58.8	52.8	55.8	23.0	23.0
8	5.3	5.3	60.8	63.8	58.8	61.8	55.4	58.4	53.4	56.4	49.7	52.7	46.7	49.7	24.5	24.5
10	6.0	6.0	59.3	62.3	57.3	60.3	53.3	56.3	51.3	54.3	47.8	50.8	44.8	47.8	25.0	25.0
16	7.6	7.6	56.2	59.2	54.2	57.2	48.7	51.7	46.7	49.7	43.7	46.7	40.7	43.7	25.0	25.0
31.25	10.7	10.7	51.9	54.9	49.9	52.9	41.2	44.2	39.2	42.2	37.9	40.9	34.9	37.9	23.6	23.6
62.5	15.4	15.4	47.4	50.4	45.4	48.4	32.0	35.0	30.0	33.0	31.9	34.9	28.9	31.9	21.5	21.5
100	19.8	19.8	44.3	47.3	42.3	45.3	24.5	27.5	22.5	25.5	27.8	30.8	24.8	27.8	20.1	20.1
200	29.0	29.0	39.8	42.8	37.8	40.8	10.8	13.8	8.8	11.8	21.8	24.8	18.8	21.8	18.0	18.0
250	32.8	32.8	38.3	41.3	36.3	39.3	5.5	8.5	3.5	6.5	19.8	22.8	16.8	19.8	17.3	17.3
300*	-	36.4	-	40.1	-	38.1	-	3.7	-	1.7	-	21.3	-	18.3	-	16.8
350*	-	39.8	-	39.1	-	37.1	-	-	-	-	-	19.9	-	16.9	-	16.3
400*	-	43.0	-	39.3	-	36.3	-	-	-	-	-	18.8	-	15.8	-	15.9
500*	-	48.9	-	36.8	-	34.8	-	-	-	-	-	16.8	-	13.8	-	15.2
555*	-	52.0	-	36.1	-	34.1	-	-	-	-	-	15.9	-	12.9	-	14.9

*Frequencies beyond the TIA and ISO requirements are for information only.

All values are dB/100m.

1. Ampacity rating per NEC 725.144 of NFPA NEC (2017) up to 192 cable bundle.