

## 74 01 250 High Leverage Diagonal Cutter



- Technical details
- Description
- Special
- Applications

	<b>No.</b>	74 01 250
	<b>EAN</b>	4003773034063
	<b>Pliers</b>	black atramentized
	<b>Head</b>	polished
	<b>Handles</b>	plastic coated
	<b>Style</b>	0
	<b>medium hard wire</b>	4,6 Ø mm
	<b>hard wire</b>	3,5 Ø mm
	<b>piano wire</b>	3,0 Ø mm
	<b>Length</b>	250 mm
	<b>Net weight</b>	391 g

- for very tough, continuous use
- high cutting performance with minimum effort due to optimum co-ordination of the cutting edge angle and transmission ratio
- precision cutting edges additionally induction hardened (cutting edge hardness approx. 64 HRC), for all sorts of wire including piano wire
- Chrome vanadium heavy-duty steel, forged, oil-hardened

Length 250 mm:

- the 250-mm-long diagonal cutter is suitable for copper conductors up to 16 mm<sup>2</sup> and aluminium conductors up to 35 mm<sup>2</sup>

### 20 % less effort required

compared to conventional diagonal cutters of the same length.

With integrated forged joint axle.



technical change and errors excepted