



U227MTBL
200A 7T RT OH MAIN
784572177055

Brand Name: Milbank

Type: Ring Type Meter Socket

Application: Meter Socket With Main And Load Center

Standard: UL Listed

Voltage Rating: Up to 240 Volts Alternating Current

Amperage Rating: 200 Continuous Ampere

Phase: 3 Phase

Frequency Rating: 60 Hertz

Size: 6H x 27W x 30H

Number Of Cutouts: 1

Cutout Size: 200 Ampere Main Breaker

Cable Entry: Overhead and Underground

Terminal: Single Mechanical Line Side and Single Mechanical Load Side Connector

Insulation: Fiberglass with Resin

Mounting: Surface Mount

Enclosure: Type 3R, G90 Galvanized Steel with Powder Coat Finish

Jaw Quantity: 7 Terminal

Bypass Type: Link Bypass


Number of Metered Positions: 1 Position

Equipment Ground: Ground Lug

Hub Opening: Small Closing Plate





Line Side Wire Range: 6 AWG - 250 kcmil

Number Receptacles: 0



Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.

| FEATURE TABLE | | |
|---------------|-----|-----------------------------------|
| ITEM | QTY | DESCRIPTION |
| A | 4 | STD. MNTG. EMBOSS |
| B | 17 | 1/2" SOLID K.O. |
| C | 7 | 1/2, 3/4 CONC. K.O. |
| D | 3 | 3/4, 1, 1 1/4, 1 1/2 CONC. K.O. |
| E | 2 | 1 1/4, 1 1/2, 2, 2 1/2 CONC. K.O. |
| F | 1 | 2, 2 1/2, 3 CONC. K.O. |



Version:

1

All dimensions are +/- 1/16".
Drawing views are not to scale.

Utility requirements for this equipment may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.