




# Wall Light

## WLMFC43LED 43 Watt LED Wall Light



### SPECIFICATIONS:

**Lumens:** 5366  
**Watts:** 41.20  
**Lumens/Watt:** 130.2  
**CRI:** 81.9  
**CCT:** 4602  
**Lifespan:** 200,000+ hrs.<sup>1</sup>



Patent Pending

### Construction:

Rugged Traditional aluminum die cast housing provides proven environmental protection for LED modules. Traditional fixture design provides a familiar look and standard installation requirements. Retaining this look allows the ability to upgrade fixtures gradually, while retaining the same overall fixture appearance throughout a facility.

### Glare Free:

Positioning of the LED modules within the housing result in light directed to desired locations and eliminates offensive light.

### Thermal Management:

Atlas' Patent Pending exclusive Thermal Management System™ features a unique internal design that allows for lower operating temperatures which results in a brighter, whiter light, more stable color and longer LED and driver life.

### Listings:

Luminaire is certified to UL Standards for Wet Locations  
 Lighting Facts Certified  
 DesignLights Consortium Premium qualified luminaire, eligible for rebates from DLC member utilities. DLC Product ID: P0000053L

### AC Input:

120/208/240/277 V

### Driver:

Constant current, Class 2, 120-277 VAC, 50-60 Hz  
 High Efficiency – min. 88%  
 Off-State Power: 0 Watts  
 0-10 V Dimming

### LEDs:

4500K CCT  
 Epoxy Guard™ protective conformal coated boards  
 Atlas LEDs provide higher lumen output, greater energy efficiency and more reliable fixture performance.

### Warranty:

Atlas Lighting Products provides a 5 year limited warranty for this product. A full warranty can be found at [www.alpinc.com](http://www.alpinc.com).

### Testing:

Atlas LED luminaires have been tested by an independent laboratory in accordance with IESNA LM-79 & LM-80, and have received the Department of Energy "Lighting Facts" label.

### Installation:

Fixture retains the same knock-out sizes and positions as previous models, reducing wiring costs.

### Photo Control:

For factory installed 120V button photo control add suffix PC to part number.

### Project Information


Job Name

Fixture Type 43 Watt LED Medium Wall Light

Catalog Number WLMFC43LED

Approved by

### DIMENSIONS:



<sup>1</sup>LED Life Span Based Upon LM-80 Test Results


**Rebates and Incentives are available in many areas.  
 Contact an Atlas Representative for more information.**

## ATLAS LIGHTING PRODUCTS, INC.

PO BOX 2348 | BURLINGTON, NC 27216  
 800-849-8485 | FAX: 336-227-0110 | [www.atlaslightingproducts.com](http://www.atlaslightingproducts.com)

\*The majority of Atlas Lighting Products are assembled in USA facilities by an American Workforce utilizing both Domestic and Foreign components. Meets Buy American requirements within the ARRA.


**PHOTOMETRIC**



**ENERGY SAVINGS**

LED		HID			ANNUAL SAVINGS
WATTAGE	ANNUAL COST	SOURCE WATTAGE	TOTAL WATTAGE USED	ANNUAL COST	
43	\$19	100	129	\$77	\$58
43	\$19	150	185	\$100	\$81
43	\$19	175	210	\$112	\$93

**MOUNTING DETAIL**



Atlas Lighting Products

**LED**  
**lighting facts**<sup>®</sup>  
A Program of the U.S. DOE

<b>Light Output (Lumens)</b>	<b>5366</b>
<b>Watts</b>	<b>41.2</b>
<b>Lumens per Watt (Efficacy)</b>	<b>130.2</b>

---

<b>Color Accuracy</b> Color Rendering Index (CRI)	<b>81</b>
--	-----------

---

<b>Light Color</b> Correlated Color Temperature (CCT)	<b>4602 (Daylight)</b>
--	------------------------

All results are according to IESNA LM-79-2008: *Approved Method for the Electrical and Photometric Testing of Solid-State Lighting*. The U.S. Department of Energy (DOE) verifies product test data and results.

**Visit [www.lightingfacts.com](http://www.lightingfacts.com) for the Label Reference Guide.**

Registration Number: PRB4-N4EZ8S (1/28/2016)  
Model Number: WLMFC43LED [Upgrade : 1/28/2016]  
Type: Luminaire - Area/Roadway