







95 62 190 Wire Rope Cutter

forged



- Technical details
- Description
- Special
- Applications

	No.	95 62 190
	EAN	4003773071976
	Head	burnished
	Handles	with multi-component grips
	piano wire	2,5 Ø mm
	Cutting capacity copper cable, multiple-stranded (diameter)	7 Ø mm
	Cutting capacity wire rope	5 Ø mm
	medium hard wire	4,0 Ø mm
	AWG	7
	Length	190 mm
	Net weight	314 g

- with two crimping dies for end caps on Bowden cable sheaths and end ferrules for traction cables
- comfortable work thanks to handy, slim design and internal opening spring
- bolted joint for precise blade guidance, re-adjustable
- high leverage for reduced effort
- cutting-edge hardness approx. 64 HRC
- Chrome vanadium heavy-duty steel, forged, oil-hardened


Cuts all wire ropes without splaying, including those that are extremely strong



Crimping of the end ferrule onto the traction cable



Crimping of the end caps on the Bowden cable sheath



Internal opening spring

technical change and errors excepted