


# 16352-1PI



Color:  Ivory

UPC Code: 07847770477

Country Of Origin: Mexico

\*Eligible for ARRA funded projects > \$7,443,000

NEMA:  
5-20R



# 16352-1PI

## Brand Features

Leviton offers custom imprinting solutions to meet the 2014 National Electrical Code requirements for identifying receptacles that will be automatically de-energized as part of an overall plug load control program. All 15A & 20A, 125V receptacles that are automatically controlled will be marked with a specific symbol.

## Item Description

20 Amp, 125 Volt, NEMA 5-20R, 2P, 3W, Decora Plus Duplex Receptacle, Straight Blade, Commercial Grade, Hot Terminal Split w/1 Plug Controlled, Self Grounding, Back & Side Wired, Contractor Pack - IVORY

## Technical Information

### AC Horsepower Ratings

**At Rated Voltage:** 1 HP

### Electrical Specifications

**Dielectric Voltage:** Withstands 2000V per UL498

**Grounding:** Self-Grounding

**Temperature Rise:** Max 30C after 250 cycles OL at 200 percent rated current

**Voltage:** 125 Volt

**Amperage:** 20 Amp

**Wire:** 3

**Pole:** 2

### Environmental Specifications

**Operating Temperature:** -40°C to 75°C

**Flammability:** Rated V-2 per UL94

### Material Specifications

**Strap Material:** Zinc-Plated Steel 0.042

**Face Material:** Nylon

**Body Material:** Nylon

**Ground Clips:** Brass

**Terminal Screws:** Brass 10-32

**Line Contacts:** Brass Triple-Wipe .031 Thick

**Terminal Clamp:** Zinc-Plated Steel

**Grounding Screw:** Zinc-Plated Steel 8-32

### Mechanical Specifications

**Product ID:** Ratings are permanently marked on device

**Wire Type:** Solid or Stranded Building Wire

**Terminal ID:** Brass-Hot, Green-Ground, Silver-Neutral

**Termination:** Back & side wiring, 8 back-wiring holes

**Terminal Accom.:** 14-10 AWG

### Product Features

**Color:** Ivory

**NEMA:** 5-20R

### Standards and Certifications

**Applicable Standards:** UL 498, CSA C22.2 No. 42


**Certification/Listing:** UL, CSA, NOM-ANCE

**ANSI:** C-73

**NEMA:** WD-1 & WD-6

### Warranty

**Warranty:** 10-Year Limited



## SPECIFICATION SUBMITTAL

JOB NAME:	CATALOG NUMBERS:	
<input type="text"/>	<input type="text"/>	<input type="text"/>
JOB NUMBER:	<input type="text"/>	<input type="text"/>

### Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Teléfono: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday): +1-800-824-3005

### Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·

FAX: +1-800-824-3005 · [www.leviton.com/canada](http://www.leviton.com/canada)

### Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-1797 · [www.leviton.com.mx](http://www.leviton.com.mx)

### Visit our Website at: [www.leviton.com](http://www.leviton.com)

© 2012 Leviton Manufacturing Co., Inc. Todos los derechos reservados. Subject to change without notice.

### Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to:

[www.leviton.com/international/contacts/](http://www.leviton.com/international/contacts/)



*\*Leviton is the smart choice, providing the most comprehensive range of solutions to meet the needs of today's residential, commercial and industrial buildings. Leveraging more than a century of experience, Leviton helps customers create sustainable, intelligent environments through its electrical wiring devices, network and data center connectivity solutions, and lighting energy management systems. From switches and receptacles, to daylight harvesting controls, networking systems, and equipment for charging electric vehicles, Leviton solutions help customers achieve savings in energy, time and cost, all while enhancing safety.*