

Control Power Transformer, 500va, PRI 208/230/460 200/220/440
240 SEC 24x115 23x110 25x120v, Domestic,



Figure similar

Product brand name	Control Power Transformer
Product designation	MT
Special product feature	Robust design

General technical data	
Weight [lb]	19.2 lb
Height x Width x Depth [in]	5.69 × 5.25 × 6.67 in
Ambient temperature [°F] during operation	-4 ... +104 °F
Ambient temperature during operation	-20 ... +40 °C
Country of origin	Mexico
Operating apparent output rated value	500 V·A

Enclosure	
Design of the housing	Open

Mounting/wiring	
Mounting position	Any
Mounting type	Surface mounting
Type of electrical connection at input for main current circuit	Screw-type terminals (touchsafe)

Inputs/ Outputs	
Input dimensions of primary voltage	208/230/460,200/220/440,240/480vac
Output dimensions of secondary voltage	24x115,23x110,25x120vac
Design of fuse holder of the secondary section	Require touchsafe cover
Phase number of the inputs	1
Electrical input frequency	50 ... 60 Hz
Input voltage _1	208 V
Input voltage _2	230 V
Input voltage _3	460 V
Input voltage _4	200 V
Input voltage _5	220 V
Input voltage _6	440 V
Input voltage _7	240 V
Input voltage _8	480 V
Phase number of the outputs	1
Electrical output frequency	60 ... 50 Hz
Output voltage _1 rated value	24 V
Output voltage _3 rated value	23 V
Output voltage _2 rated value	115 V
Output voltage _4 rated value	110 V
Output voltage _5 rated value	25 V
Output voltage _6 rated value	120 V

Certificates/approvals	
Certificate of suitability	UL / CSA

Further information	
Service&Support (Manuals, Certificates, Characteristics, FAQs,...) https://support.industry.siemens.com/cs/US/en/ps/US2:MT0500J	

last modified: 08/07/2017