

Siemens Low Voltage Circuit Protection Heavy Duty Safety Switch.  
3-Pole Non-Fused in a type 12 industrial enclosure. Rated 600VAC  
(100A).



Manner of function of the actuating element	SINGLE THROW
Mechanical service life (switching cycles) typical	10000
Mounting type	2 OR 3 POINT MOUNTING HOLES
Number of poles	3

Electricity	
Ampacity	100 A
Supply voltage frequency rated value 50/60 Hz	Yes
Voltage between phase and Ground (GND) rated value	600 V

Switching capacity	
Switching capacity active power	3 W

Model	
Product brand name	SIEMENS
Product type designation	ENCLOSED/SAFETY SWITCH

Mechanical Design	
Design of the housing	TYPE 12
Material	304SS

General product approval	
--------------------------	--

**last modified:**

03/12/2018