

Control Power Transformer, 1000va, PRI 240x480 230x460 220
440v, SEC 120/115/110v, Domestic,



Figure similar

Product brand name	Control Power Transformer
Product designation	MT
Special product feature	Robust design
General technical data	
Weight [lb]	30 lb
Height x Width x Depth [in]	6.62 × 7 × 6.42 in
Ambient temperature [°F] during operation	-4 ... +104 °F
Ambient temperature during operation	-20 ... +40 °C
Country of origin	Mexico
Operating apparent output rated value	1000 V·A
Enclosure	
Design of the housing	Open
Mounting/wiring	
Mounting position	Any
Mounting type	Surface mounting
Type of electrical connection at input for main current circuit	Screw-type terminals (touchsafe)

Inputs/ Outputs	
Input dimensions of primary voltage	240x480,230x460,220x440vac
Output dimensions of secondary voltage	120/115/110vac
Design of fuse holder of the secondary section	Require touchsafe cover
Phase number of the inputs	1
Electrical input frequency	50 ... 60 Hz
Input voltage _1	240 V
Input voltage _2	480 V
Input voltage _3	230 V
Input voltage _4	460 V
Input voltage _5	220 V
Input voltage _6	440 V
Phase number of the outputs	1
Electrical output frequency	60 ... 50 Hz
Output voltage _1 rated value	120 V
Output voltage _3 rated value	110 V
Output voltage _2 rated value	115 V

Certificates/approvals	
Certificate of suitability	UL / CSA

Further information

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)
<https://support.industry.siemens.com/cs/US/en/ps/US2:MT1000A>

last modified: 08/07/2017