


## PS 888 – Four-Hole Splice Plate



Weight/100 pcs: 78 lbs.

### MATERIAL:

All Power-Strut fittings are formed in punch press dies from mild, pickled and oiled, bar or strip steel. Plain or electro-galvanized fittings meet the requirements for ASTM A575 and A-576, or ASTM A-36.

### STANDARD DIMENSIONS:

Standard dimensions on all fittings are as follows except where otherwise indicated:

Fitting Thickness: 1/4"  
 Fitting Width: 15/8"  
 Hole Diameter: 9/16"  
 Hole Spacing: 17/8" on centers & 13/16" from ends.

### STANDARD FINISH:

All Power-Strut fittings are available in painted green or electro-galvanized finish.

### POWER-STRUT® DEFENDER™ FINISH [DF]:

Power-Strut Defender is a combination of two proprietary material coatings conforming to ASTM standards A1046 and A1059. It features unique self-healing properties.



### ORDERING INFORMATION:

When ordering, add the length or size and finish to the part number.

Project: \_\_\_\_\_  
 Architect / Engineer: \_\_\_\_\_  
 Date: \_\_\_\_\_ Phone: \_\_\_\_\_  
 Contractor: \_\_\_\_\_  
 Address: \_\_\_\_\_  
 \_\_\_\_\_  
 Notes 1: \_\_\_\_\_  
 \_\_\_\_\_  
 Notes 2: \_\_\_\_\_  
 \_\_\_\_\_

Approval Stamp: