



Powering Business Worldwide

pe.eaton.com

Quicklag Industrial Ground Fault Thermal-Magnetic Equipment Breaker

QBHGFEP1020

UPC:786679039526

Dimensions:

- **Height:** 1.1 IN
- **Length:** 5.1 IN
- **Width:** 3.2 IN

Weight:.4 LB

Warranties:

- 1 year

Specifications:

- **Type:** Quicklag
- **Special Features:** 30 mA Sensitivity
- **Amperage Rating:** 20A
- **Interrupt Rating:** 22 kAIC
- **Number Of Poles:** Single-pole
- **Voltage Rating:** 120V
- **Circuit Breaker Type:** QBHGF
- **Trip Type:** Non-Interchangeable
- **Mounting:** Bolt-on

Supporting documents:

- [Circuit Breaker Time/Current Curves For QUICKLAG. Industrial Circuit Breakers](#)
- [Eatons Volume 4-Circuit Protection](#)

Certifications:

- UL Listed
- CSA Certified

Product compliance: No Data

