

19645 - GE Starcoat® T8

F15T8/SPX35

PRODUCT PHOTO



GENERAL CHARACTERISTICS

Base Description	Medium Bi-Pin (G13)
Base Type	Pin/Plug-In
Mercury Content	18 mg
Mercury-Picogram per mean lm hr	2666.7
Starting Temp (MIN) C-degrees	10 °C
Bulb Material	Soda lime
Rated Life Hours-nominal	7500 h
Primary Application	Full Wattage
Product Technology	Linear Fluorescent
Base	G13
Bulb Shape	T8

PHOTOMETRIC CHARACTERISTICS

Mean Lumens nominal	900 lm
Nominal Initial Lumen per Watt	66.6666666667
Initial Lumens-nominal	1000 lm
Color Temperature	3500 K

PRODUCT INFORMATION

Product Code	19645
Description	F15T8/SPX35
Alternative Unit Of Measure	CASE
Standard Package Quantity	24
Ean UPC	043168196451
Standard Package GTIN	10043168196458
No Of Items Per Sales Unit	
No Of Items Per Standard Package	24
Sales Unit	Case
UCC	043168196451
Alternative Unit Of Measure	EACH
Standard Package Quantity	1
Ean UPC	043168196451
Standard Package GTIN	00043168196451
No Of Items Per Sales Unit	
No Of Items Per Standard Package	1
Sales Unit	Each
UCC	

DIMENSIONS

Bulb Diameter (DIA) <Max>	1.1 in
Bulb Diameter (DIA) <Min>	0.94 in
Diameter	1.0 in
End of Base Pin to Pin	17.67 in
Face to End of Opposing Pin (B) <Max>	17.5 in
Face to End of Opposing Pin (B) <Min>	17.39 in
Nominal Length	18.0 in

ELECTRICAL CHARACTERISTICS

Current Crest Factor (MAX)	1.7
Open Circuit Voltage (rapid start) Min @ Temperature	157.00 V @ 10 °C
Cathode Resistance Ratio - Rh/Rc (MIN)	4.250
Cathode Resistance Ratio - Rh/Rc (MAX)	6.500
Rated power (Watts)	15 W

CAUTIONS & WARNINGS

Caution

- Lamp may shatter and cause injury if broken
- Wear safety glasses and gloves when handling lamp.
- Do not use excessive force when installing lamp.

Warning

- Risk of Electric Shock

Turn power off before inspection
installation or removal.

