

# LMSM-ENC1 Enclosure for LMSM Segment Manager

NEMA1-rated enclosure

Isolated Class 1 and Class 2 wiring

Compatible with LMSM-201 or LMSM-603



DIN rail mounting for easy installation or removal of Segment Manager

Shown with Segment Manager installed

PROJECT
LOCATION/TYPE

## Product Overview

### Description

The LMSM-ENC1 is a surface-mount NEMA1-rated enclosure with a DIN rail for mounting one LMSM Segment Manager, conduit knockouts for line and low voltage connections and a removable cover. The conduit entrances and enclosure sections for high voltage (Class 1) and low voltage (Class 2) wiring are completely separated.


### Applications

The LMSM-ENC1 allows a Segment Manager to be installed in an electrical room or other location with similar requirements. The enclosure accommodates one LMSM-201 or LMSM-603 Segment Manager.

### Specifications

- Input voltage: 120VAC, 50/60Hz
- Duplex receptacle for connection of LMSM plug-in power supply
- Barrier between high and low voltage
- DIN rail for mounting LMSM, includes locking tab
- Housing: NEMA1 surface-mount enclosure with screw-on cover, suitable for damp locations
- UL and cUL listed
- Five year warranty

### Dimensions and Mounting



## Ordering Information

Catalog No.	Description
<input type="checkbox"/> LMSM-ENC1	NEMA1 surface mount enclosure for Segment Manager (order Segment Manager separately)