

111-01560

HellermannTyton



Article Number: 111-01560

Description: Solar Tie, 8" Long, 45lb Tensile Strength, PA12, Black, 100/pkg

Base Data		
	Local Order Number	111-01560
	Type	T50R
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> • Nylon 12 cable ties provide excellent resistance to UV, chemical and moisture sensitive environments. • Inside serrations and smooth edges allow for a strong hold on cables and wire bundles without damaging them. • Head design provides high tensile strength with very low insertion force.
	Quantity Per	bag
	Product Description	HellermannTyton standard cable ties feature inside serrations providing a positive hold onto wire and cable bundles. The head design guarantees high tensile strength, as well as a low insertion force. The bent tail design allows quick and simple installations by hand. For high volume applications, tensioning tools are available to ensure consistent and safe installation.
	Global Part Name	T50R-PA12-BK
	Short Description	Solar Tie, 8" Long, 45lb Tensile Strength, PA12, Black, 100/pkg
Product Dimensions		
	Minimum Tensile Strength (Imperial)	45lbs
	Minimum Tensile Strength (Metric)	200.0N
	Length L (Imperial)	8.0"
	Length L (Metric)	202.0mm
	Fixation Method	None
	Identification Plate Position	none
	Releasable Closure	No
	Tie Closure	plastic pawl
	Variant	Inside Serrated
	Width W (Imperial)	0.18"
	Width W (Metric)	4.6mm
	Bundle Diameter Min. (Imperial)	0.06"

111-01560

HellermannTyton

Product Dimensions	Bundle Diameter Min. (Metric)	1.5mm
	Bundle Diameter Max. (Imperial)	1.97"
	Bundle Diameter Max. (Metric)	50.0mm
	Thickness T (Metric)	1.2mm
Material and Specifications		
	Material	Polyamide 12 (PA12)
	Material Shortcut	PA12
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	100
	Package Quantity (Metric)	100
	Customs Number(Schedule B)	3926909987