

INDICATOR LIGHT, 22MM, ROUND, METAL, SHINY, AMBER, SMOOTH LENS, WITH HOLDER, LED MODULE, WITH INTEGRATED LED 110V AC, SCREW TERMINAL



Figure similar

|   |                                    |
|---|------------------------------------|
| product brand name                      | SIRIUS ACT                         |
| Product designation                     | Commanding and signaling devices   |
| Design of the product                   | Pilot Light                        |
| Manufacturer article number             |                                    |
| • of supplied repeater                  | <a href="#">3SU1051-6AA00-0AA0</a> |
| <b>Actuator:</b>                        |                                    |
| Product expansion optional Light source | Yes                                |
| Color                                   |                                    |
| • of the actuating element              | Amber                              |
| Material of the actuating element       | plastic                            |
| Shape of the actuating element          | round                              |
| Outer diameter of the actuating element | 29.45 mm                           |
| <b>Front ring:</b>                      |                                    |
| Product component front ring            | No                                 |
| <b>Holder:</b>                          |                                    |
| Material of the holder                  | Metal                              |
| <b>Display:</b>                         |                                    |
| Number of LED modules                   | 1                                  |

| General technical data:  |                                   |
|--|-----------------------------------|
| <b>Product component</b>   |                                   |
| • Light source   | Yes                               |
| <b>Insulation voltage</b>  |                                   |
| • Rated value  | 320 V                             |
| <b>Surge voltage resistance Rated value</b>                      | 4 kV                              |
| <b>Protection class IP</b>                                       | IP66, IP67, IP69(IP69K)           |
| • of the terminal  | IP20                              |
| <b>Degree of pollution</b>                                       | 3                                 |
| <b>Shock resistance</b>  |                                   |
| • acc. to IEC 60068-2-27   | Sinusoidal half-wave 50 g / 11 ms |
| <b>Vibration resistance</b>                                      |                                   |
| • acc. to IEC 60068-2-6  | 10 ... 500 Hz: 5g                 |
| <b>Equipment marking</b>   |                                   |
| • acc. to DIN EN 61346-2   | P                                 |
| • acc. to DIN EN 81346-2   | P                                 |
| <b>Relative positive tolerance of the operating voltage</b>      | 20 %                              |
| <b>Relative negative tolerance of the operating voltage</b>      | 20 %                              |
| Auxiliary circuit:   |                                   |
| <b>Number of NC contacts</b>                                     |                                   |
| • for auxiliary contacts   | 0                                 |
| <b>Number of NO contacts</b>                                     |                                   |
| • for auxiliary contacts   | 0                                 |
| <b>Number of CO contacts</b>                                     |                                   |
| • for auxiliary contacts   | 0                                 |
| Connections/ Terminals:  |                                   |
| <b>Type of electrical connection</b>                             |                                   |
| • of modules and accessories                                     | Screw-type terminal               |
| <b>Tightening torque</b>   |                                   |
| • with screw-type terminals                                      | 0.8 ... 0.9 N·m                   |
| Lamp:  |                                   |
| <b>Type of light source</b>                                      | LED                               |
| <b>Color of the light source</b>                                 | amber                             |
| Ambient conditions:  |                                   |
| <b>Ambient temperature</b>                                       |                                   |
| • during operation   | -25 ... +70 °C                    |
| • during storage   | -40 ... +80 °C                    |
| <b>Environmental category during operation acc. to IEC 60721</b> | 3K6, 3C3, 3S2, 3M6                |
| Installation/ mounting/ dimensions:                              |                                   |

|  |                      |
|--|----------------------|
| <b>Mounting type</b>                     | front panel mounting |
| • of modules and accessories             | Front plate mounting |
| <b>Height</b>                            | 40 mm                |
| <b>Width</b>                             | 30 mm                |
| <b>Shape of the installation opening</b> | round                |
| <b>Mounting diameter</b>                 | 22 mm                |
| <b>Mounting height</b>                   | 11.8 mm              |
| <b>Installation width</b>                | 29.5 mm              |
| <b>Installation depth</b>                | 49.7 mm              |

#### Certificates/ approvals:

**Declaration of Conformity**

**other**

[Bestätigungen](#)



#### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/industrial-controls/catalogs>

**Industry Mall (Online ordering system)**

<http://www.siemens.com/industrymall>

**Cax online generator**


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU11536AA001AA0>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**


<https://support.industry.siemens.com/cs/ww/en/ps/3SU11536AA001AA0>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3SU11536AA001AA0&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU11536AA001AA0&lang=en)



**-P**  
**110 V AC**



last modified:

25.08.2015