




# HBL5965VBLK -- Valise Plug



2P3W, 15A 125V, 5-15P, Black Nylon

| Product Specifications |  |
|------------------------|--|
| Product Type           |  <p>Plugs</p>   |
| Body Style             | Straight   |
| Standard               | NEMA   |
| Amperage               | 15A  |
| Voltage                | 125V   |
| Poles and Wires        | 2 Pole, 3 Wire Grounding   |
| Hospital Grade ?       | No   |
| Plug/Connector Grade   | Valise   |
| Color                  |  <p>Black</p> |
| NEMA No.               | 5-15P  |
| Horsepower             | 0.5  |
| Cord Dia.              | .220"-.660" (5.6-16.8)   |
| Description            | Straight Blade Plug  |
| Type                   | 2 Pole, 3 Wire, Grounding  |

|                                      |   |
|--------------------------------------|---|
| <b>Rating</b>                        | 15A,125V  |
| <b>Certification</b>                 | UL Listed to UL498 File E1706, CSA Certified to C22.2 No. 42 File 280   |
| <b>IP Suitability</b>                | IP20  |
| <b>Housing Material</b>              | Nylon   |
| <b>Cord Clamp Material</b>           | Noryl (Polyphenylene Oxide)   |
| <b>Contact Blades Material</b>       | .060" (1.5) Brass   |
| <b>Ground Contact Blade Material</b> | .040" (1.0) Brass   |
| <b>Terminal Screw Material</b>       | Steel (copper or nickel finish)   |
| <b>Ground Screw Material</b>         | Steel (green finish)  |
| <b>Wire Clamps Material</b>          | .062" (1.8) Steel-nickel finish   |
| <b>Cable Inserts Material</b>        | Poly Phenylene Oxide  |
| <b>Body Holding Screws</b>           | Steel Multiple Drive  |
| <b>Dielectric Voltage</b>            | Withstands 2,000V minimum.  |
| <b>Current Interrupting</b>          | Certified for current interrupting at full rated current.   |
| <b>Temperature Rise</b>              | Max 30°C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of 75%.. |
| <b>Terminal Identification</b>       | Terminals identified in accordance with UL498 (Brass, White, Green).  |
| <b>Terminal Accommodation</b>        | #18-#10 AWG copper stranded conductor   |
| <b>Product Identification</b>        | Ratings are a permanent part of the device.   |
| <b>Flammability</b>                  | UL 94 V2.   |
| <b>Operating Temperatures</b>        | Maximum continuous 75°C, minimum -40°C (w/o impact).  |
| <b>M Drawings</b>                    | <a href="#">Click here for M-Drawing</a>  |
| <b>Catalog Page</b>                  | <a href="#">Click here for catalog page A22</a>   |
| <b>Brochures</b>                     | <a href="#">Click here for product brochure</a>   |
| <b>Hubbellnet</b>                    | <a href="#">Click here for Hubbellnet</a>   |
| <b>Catalog Section</b>               | <a href="#">Click here for Section-A</a>  |
| <b>UPC Number</b>                    | 78358501308   |
| <b>Weight in LBs</b>                 | 0.15  |



**Hubbell Incorporated (Delaware)**  
**185 Plains Road**  
**Milford, CT 06460-2420**  
**Ph: (203) 882-4800**  
**Fax: (800) 255-1031**

