

SIMATIC HMI, KTP1200 BASIC, BASIC PANEL, KEY AND TOUCH OPERATION, 12" TFT DISPLAY, 65536 COLORS, PROFINET INTERFACE, CONFIGURATION FROM WINCC BASIC V13/ STEP7 BASIC V13, CONTAINS OPEN SOURCE SW WHICH IS PROVIDED FREE OF CHARGE FOR DETAILS SEE CD



## General information

Product type designation      KTP1200 Basic color PN

## Display

Design of display      TFT widescreen display, LED backlighting

Screen diagonal      12 in

Display width      261.1 mm

Display height      163.2 mm

Number of colors      65 536

### Resolution (pixels)

- Horizontal image resolution      1 280 Pixel
- Vertical image resolution      800 Pixel

### Backlighting

- MTBF backlighting (at 25 °C)      20 000 h
- Backlight dimmable      Yes

## Control elements

### Keyboard fonts

- Function keys
  - Number of function keys      10

• Keys with LED	No
• System keys	No
• Numeric keyboard	Yes; Onscreen keyboard
• alphanumeric keyboard	Yes; Onscreen keyboard
<b>Touch operation</b>	
• Design as touch screen	Yes
<b>Installation type/mounting</b>	
Mounting position	Horizontal, vertical
Mounting in portrait format possible	Yes
Mounting in landscape format possible	Yes
maximum permissible angle of inclination without external ventilation	35°
<b>Supply voltage</b>	
Type of supply voltage	DC
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
<b>Input current</b>	
Current consumption (rated value)	510 mA
Starting current inrush I <sup>2</sup> t	0.2 A <sup>2</sup> ·s
<b>Power</b>	
Active power input, typ.	12.2 W
<b>Processor</b>	
Processor type	ARM
<b>Memory</b>	
Flash	Yes
RAM	Yes
Memory available for user data	10 Mbyte
<b>Type of output</b>	
Acoustics	
• Buzzer	Yes
• Speaker	No
<b>Time of day</b>	
Clock	
• Hardware clock (real-time)	Yes
• Software clock	Yes
• retentive	Yes; Back-up duration typically 6 weeks
• synchronizable	Yes
<b>Interfaces</b>	

Number of industrial Ethernet interfaces	1
Number of RS 485 interfaces	0
Number of RS 422 interfaces	0
Number of RS 232 interfaces	0
Number of USB interfaces	1; Up to 16 GB
Number of 20 mA interfaces (TTY)	0
Number of parallel interfaces	0
Number of other interfaces	0
Number of SD card slots	0
With software interfaces	No
<b>Industrial Ethernet</b>	
• Industrial Ethernet status LED	2

<b>Protocols</b>	
PROFINET	Yes
Supports protocol for PROFINET IO	No
IRT	No
MRP	No
PROFIBUS	No
MPI	No

<b>Protocols (Ethernet)</b>	
• TCP/IP	Yes
• DHCP	Yes
• SNMP	Yes
• DCP	Yes
• LLDP	Yes

<b>WEB characteristics</b>	
• HTTP	No
• HTML	No

<b>Further protocols</b>	
• CAN	No
• EtherNet/IP	Yes
• MODBUS	Yes; Modicon (MODBUS TCP/IP)

<b>Interrupts/diagnostics/status information</b>	
<b>Diagnostic messages</b>	
• Diagnostic information readable	No

<b>EMC</b>	
<b>Emission of radio interference acc. to EN 55 011</b>	
• Limit class A, for use in industrial areas	Yes
• Limit class B, for use in residential areas	No

<b>Degree and class of protection</b>	
IP (at the front)	IP65

Enclosure Type 4 at the front	Yes
Enclosure Type 4x at the front	Yes
IP (rear)	IP20

### Standards, approvals, certificates

CE mark	Yes
cULus	Yes
RCM (formerly C-TICK)	Yes
KC approval	Yes

### Marine approval

<ul style="list-style-type: none"> <li>• Germanischer Lloyd (GL)</li> <li>• American Bureau of Shipping (ABS)</li> <li>• Bureau Veritas (BV)</li> <li>• Det Norske Veritas (DNV)</li> <li>• Lloyds Register of Shipping (LRS)</li> <li>• Nippon Kaiji Kyokai (Class NK)</li> <li>• Polski Rejestr Statkow (PRS)</li> <li>• Chinese Classification Society (CCS)</li> </ul>	<ul style="list-style-type: none"> <li>Yes</li> <li>Yes</li> <li>Yes</li> <li>Yes</li> <li>Yes</li> <li>Yes</li> <li>No</li> <li>No</li> </ul>
--	--

### Use in hazardous areas

<ul style="list-style-type: none"> <li>• ATEX Zone 2</li> <li>• ATEX Zone 22</li> <li>• IECEx Zone 2</li> <li>• IECEx Zone 22</li> <li>• cULus Class I Zone 1</li> <li>• cULus Class I Zone 2, Division 2</li> <li>• FM Class I Division 2</li> </ul>	<ul style="list-style-type: none"> <li>No</li> <li>No</li> <li>No</li> <li>No</li> <li>No</li> <li>No</li> <li>No</li> </ul>
---	--

### Ambient conditions

#### Ambient temperature during operation

<ul style="list-style-type: none"> <li>• Operation (vertical installation) <ul style="list-style-type: none"> <li>— For vertical installation, min.</li> <li>— For vertical installation, max.</li> </ul> </li> <li>• Operation (max. tilt angle) <ul style="list-style-type: none"> <li>— At maximum tilt angle, min.</li> <li>— At maximum tilt angle, min.</li> </ul> </li> <li>• Operation (vertical installation, portrait format) <ul style="list-style-type: none"> <li>— For vertical installation, min.</li> <li>— For vertical installation, max.</li> </ul> </li> <li>• Operation (max. tilt angle, portrait format) <ul style="list-style-type: none"> <li>— At maximum tilt angle, min.</li> <li>— At maximum tilt angle, min.</li> </ul> </li> </ul>	<ul style="list-style-type: none"> <li>0 °C</li> <li>50 °C</li> <li>0 °C</li> <li>40 °C</li> <li>0 °C</li> <li>40 °C</li> <li>0 °C</li> <li>35 °C</li> </ul>
--	--

#### Ambient temperature during storage/transportation

<ul style="list-style-type: none"> <li>• min.</li> </ul>	-20 °C
--	--------

• max.	60 °C
<b>Relative humidity</b>	
• Operation, max.	90 %; no condensation
<b>Operating systems</b>	
proprietary	Yes
<b>pre-installed operating system</b>	
• Windows CE	No
<b>Configuration</b>	
Message indicator	Yes
Alarm system (incl. buffer and acknowledgment)	Yes
Process value display (output)	Yes
Process value default (input) possible	Yes
Recipe management	Yes
<b>Configuration software</b>	
• STEP 7 Basic (TIA Portal)	Yes; via integrated WinCC Basic (TIA Portal)
• STEP 7 Professional (TIA Portal)	Yes; via integrated WinCC Basic (TIA Portal)
• WinCC flexible Compact	No
• WinCC flexible Standard	No
• WinCC flexible Advanced	No
• WinCC Basic (TIA Portal)	Yes
• WinCC Comfort (TIA Portal)	Yes
• WinCC Advanced (TIA Portal)	Yes
• WinCC Professional (TIA Portal)	Yes
<b>Languages</b>	
<b>Online languages</b>	
• Number of online/runtime languages	10
<b>Project languages</b>	
• Languages per project	32
<b>Functionality under WinCC (TIA Portal)</b>	
Libraries	Yes
<b>Applications/options</b>	
• Web browser	Yes
• SIMATIC WinCC Sm@rtServer	Yes; Available with WinCC (TIA Portal) V14 or higher
Number of Visual Basic Scripts	No
<b>Task planner</b>	
• time-controlled	No
• task-controlled	Yes
<b>Help system</b>	
• Number of characters per info text	500
<b>Message system</b>	
• Number of alarm classes	32

• Bit messages	
— Number of bit messages	1 000
• Analog messages	
— Number of analog messages	25
• S7 alarm number procedure	No
• System messages HMI	Yes
• System messages, other (SIMATIC S7, Sinumerik, Simotion, etc.)	Yes; System message buffer of the SIMATIC S7-1200 and S7-1500
• Number of characters per message	80
• Number of process values per message	8
• Acknowledgment groups	Yes
• Message indicator	Yes
• Message buffer	
— Number of entries	256
— Circulating buffer	Yes
— retentive	Yes
— maintenance-free	Yes
<b>Recipe management</b>	
• Number of recipes	50
• Data records per recipe	100
• Entries per data record	100
• Size of internal recipe memory	256 kbyte
• Recipe memory expandable	No
<b>Variables</b>	
• Number of variables per device	800
• Number of variables per screen	100
• Limit values	Yes
• Multiplexing	Yes
• Structures	No
• Arrays	Yes
<b>Images</b>	
• Number of configurable images	250
• Permanent window/default	Yes
• Global image	Yes
• Pop-up images	No
• Slide-in images	No
• Image selection by PLC	Yes
• Image number in the PLC	Yes
<b>Image objects</b>	
• Number of objects per image	100
• Text fields	Yes

• I/O fields	Yes
• Graphic I/O fields (graphics list)	Yes
• Symbolic I/O fields (text list)	Yes
• Date/time fields	Yes
• Switches	Yes
• Buttons	Yes
• Graphic display	Yes
• Icons	Yes
• Geometric objects	Yes
<b>Complex image objects</b>	
• Number of complex objects per screen	10
• Alarm view	Yes
• Trend view	Yes
• User view	Yes
• Status/control	No
• Sm@rtClient view	No
• Recipe view	Yes
• f(x) trend view	No
• System diagnostics view	Yes; System message buffer of the SIMATIC S7-1200 and S7-1500
• Media Player	No
• HTML browser	Yes
• PDF display	No
• IP camera display	No
• Bar graphs	Yes
• Sliders	No
• Pointer instruments	No
• Analog/digital clock	No
<b>Lists</b>	
• Number of text lists per project	300
• Number of entries per text list	100
• Number of graphics lists per project	100
• Number of entries per graphics list	100
<b>Archiving</b>	
• Number of archives per device	2; One message and one process value archive
• Number of entries per archive	10 000
• Message archive	Yes
• Process value archive	Yes
• Archiving methods	
— Sequential archive	Yes
— Short-term archive	Yes

• Memory location	
— Memory card	No
— USB memory	Yes
— Ethernet	No
• Data storage format	
— CSV	No
— TXT	Yes
— RDB	No
<b>Security</b>	
• Number of user groups	50
• Number of user rights	32
• Number of users	50
• Password export/import	Yes
• SIMATIC Logon	No
<b>Character sets</b>	
• Keyboard fonts	
— US English	Yes
<b>Transfer (upload/download)</b>	
• MPI/PROFIBUS DP	No
• USB	No
• Ethernet	Yes
• using external storage medium	Yes
<b>Process coupling</b>	
• S7-1200	Yes
• S7-1500	Yes
• S7-200	Yes
• S7-300/400	Yes
• LOGO!	Yes
• WinAC	Yes
• SINUMERIK	Yes; No access to NCK data
• SIMOTION	Yes
• Allen Bradley (EtherNet/IP)	Yes
• Allen Bradley (DF1)	No
• Mitsubishi (MC TCP/IP)	Yes
• Mitsubishi (FX)	No
• OMRON (FINS TCP)	No
• OMRON (LINK/Multilink)	No
• Modicon (Modbus TCP/IP)	Yes
• Modicon (Modbus)	No
<b>Service tools/configuration aids</b>	
• Backup/Restore manually	Yes



- |                                |     |
|--------------------------------|-----|
| • Backup/Restore automatically | No  |
| • Simulation                   | Yes |
| • Device switchover            | Yes |

### Peripherals/Options

#### Peripherals

- |  |     |
|--|-----|
| • Printer  | No  |
| • SIMATIC HMI MM memory card: Multi Media Card           | No  |
| • SIMATIC HMI SD memory card: Secure Digital memory card | No  |
| • SIMATIC HMI CF memory card Compact Flash Card          | No  |
| • USB memory   | Yes |
| • SIMATIC IPC USB Flashdrive (USB stick)                 | Yes |
| • SIMATIC HMI USB stick                                  | Yes |

### Mechanics/material

#### Enclosure material (front)

- |                   |     |
|-------------------|-----|
| • Plastic         | Yes |
| • Aluminum        | No  |
| • Stainless steel | No  |

### Dimensions

Width of the housing front	330 mm
Height of housing front	245 mm
Mounting cutout, width	310 mm
Mounting cutout, height	221 mm
Overall depth	60 mm

### Weights

Weight without packaging	1 710 g
Weight incl. packaging	2.2 kg

**last modified:** 10/26/2017