



GREENLEE.
A Textron Company

MADE FOR THE TRADE!™



PUMP,FOOT-HYD (1725-M3)

Hydraulic Foot Pump

Cat No: 1725

UPC No: 783310313533

Description

- Free both hands to position and hold the working tool
- Foot activated release lever
- Hold-down pin keeps pedal down for storage and transport
- Angled base bar keeps the pump upright and stable
- Includes 1/4 IN (6.4 mm) female coupler with dust cap

Specifications

- Capacity : 6,500 PSI (448 Bar), 0.117 CU-IN (19.000 CU-MM) Per Stroke
- Coupler Size : 1/4 IN
- Height : Pedal Down 6.000 IN (152.000 MM), Pedal Up 12.000 IN (305.000 MM)
- Includes : 1/4 IN (6.400 MM) Female Coupler With Dust Cap
- Length : 16.000 IN (406.000 MM)
- Operation : Manual - Foot
- Pressure Rating : 6500 PSI (448 Bar)
- Replacement Part : 24496 Seal Kit, 25214 Seal Kit, 33336 Seal Kit
- Type : Foot-Operated
- Weight : 11.000 LB (5.000 KG)
- Width : 8.000 IN (203.000 MM)