

# KTLD-100-UV-24V CONSTANT VOLTAGE LED DRIVER







### **DESCRIPTION**

LED Driver | 100W | 24V Constant Voltage Output | 120-277V Input

**DRIVER TYPE:** Constant Voltage LED Driver

MAX. POWER: 96W

INPUT VOLTAGE: 120-277Vac ±10%

**OUTPUT VOLTAGE: 24Vdc DIMMING:** Fixed Output **WARRANTY:** 5 Years



#### PRODUCT FEATURES

- Meets FCC 47 CFR Part 15 (Class B) Consumer Limits at 120V Input and (Class A) Non-Consumer Limits at 277V Input
- Over Current and Short Circuit Protection
- Type 1 Outdoor, Suitable for Dry and Damp Locations
- UL 8750 Recognized Component LED Power Unit

- Class 2 Output
- 90°C/194°F Maximum Case Temperature
- Input Frequency: 50/60 Hz
- THD: < 20%


# SPECIFICATIONS

# **ELECTRICAL SPECIFICATIONS**

	INPUT CHARACTERISTICS				OUTPUT CHARACTERISTICS				FEATURES
Family	Input Voltage	Input Power	Power Factor	Max. Current	Max. Output Power	Max. Current	Min. Current	Output Voltage	Efficiency
100W	120-277Vac	110W	>0.9	0.94A @ 120V 0.41A @ 277V	96W	4A	OA	24Vdc	87%

#### PHYSICAL SPECIFICATIONS

#### **CASE DIMENSIONS**



LENGTH	9.50"
WIDTH	1.70"
HEIGHT	1.18"
MOUNTING	8.90"
CASE STYLE	L5

#### STANDARD LEAD LENGTHS\*


BLACK	12.00"
WHITE	12.00"
BLUE	12.00"
RED	12.00"

\*Consult Keystone for special lead length requirements.


Lead wires are 18 AWG 105°C/600V, solid copper.

**CASE MATERIAL:** Metal

# WIRING DIAGRAM



# **HOT SPOT LOCATION**



Actual to point is noted on each LED driver label.

Keystone Technologies • 208 Progress Drive, Montgomeryville, PA 18936 • Phone (800) 464-2680 • Fax (888) 966-0556 • www.keystoneballast.com



# KTLD-100-UV-24V CONSTANT VOLTAGE LED DRIVER

# **ORDERING INFORMATION**

ORDER CODE	PACKAGING STYLE	PACK QTY.	ITEM STATUS
KTLD-100-UV-24V-CP	Carton Pack	Pending	Active

# **CATALOG NUMBER BREAKDOWN**

