

SIMATIC DP, CPU 1510SP-1 PN for ET 200SP, Central processing unit with Work memory 100 KB for program and 750 KB for data, 1st interface: PROFINET IRT with 3-port switch, 72 ns bit performance, SIMATIC Memory Card required, BusAdapter required for Port 1 and 2



General information	
Product type designation	CPU 1510SP-1 PN
HW functional status	FS03
Firmware version	V2.5
Product function	
<ul style="list-style-type: none"> I&M data 	Yes; I&M0 to I&M3
<ul style="list-style-type: none"> Module swapping during operation (hot swapping) 	Yes; Multi-hot swapping
Engineering with	
<ul style="list-style-type: none"> STEP 7 TIA Portal configurable/integrated as of version 	V15 (FW V2.5) / V13 SP1 Update 4 (FW V1.8) or higher
Configuration control	
via dataset	Yes
Control elements	
Mode selector switch	1
Supply voltage	
Type of supply voltage	24 V DC
permissible range, lower limit (DC)	19.2 V

permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Mains buffering	
• Mains/voltage failure stored energy time	5 ms
Input current	
Current consumption (rated value)	0.6 A
Inrush current, max.	4.7 A; Rated value
I^2t	0.14 A ² ·s
Power	
Infeed power to the backplane bus	8.75 W
Power loss	
Power loss, typ.	5.6 W
Memory	
Number of slots for SIMATIC memory card	1
SIMATIC memory card required	Yes
Work memory	
• integrated (for program)	100 kbyte
• integrated (for data)	750 kbyte
Load memory	
• Plug-in (SIMATIC Memory Card), max.	32 Gbyte
Backup	
• maintenance-free	Yes
CPU processing times	
for bit operations, typ.	72 ns
for word operations, typ.	86 ns
for fixed point arithmetic, typ.	115 ns
for floating point arithmetic, typ.	461 ns
CPU-blocks	
Number of elements (total)	2 000; Blocks (OB, FB, FC, DB) and UDTs
DB	
• Number range	1 ... 60 999; subdivided into: number range that can be used by the user: 1 ... 59 999, and number range of DBs created via SFC 86: 60 000 ... 60 999
• Size, max.	750 kbyte; For DBs with absolute addressing, the max. size is 64 KB
FB	
• Number range	0 ... 65 535
• Size, max.	100 kbyte
FC	
• Number range	0 ... 65 535
• Size, max.	100 kbyte

OB	
• Size, max.	100 kbyte
• Number of free cycle OBs	100
• Number of time alarm OBs	20
• Number of delay alarm OBs	20
• Number of cyclic interrupt OBs	20; With minimum OB 3x cycle of 500 µs
• Number of process alarm OBs	50
• Number of DPV1 alarm OBs	3
• Number of isochronous mode OBs	1
• Number of technology synchronous alarm OBs	2
• Number of startup OBs	100
• Number of asynchronous error OBs	4
• Number of synchronous error OBs	2
• Number of diagnostic alarm OBs	1
Nesting depth	
• per priority class	24
Counters, timers and their retentivity	
S7 counter	
• Number	2 048
Retentivity	
— adjustable	Yes
IEC counter	
• Number	Any (only limited by the main memory)
Retentivity	
— adjustable	Yes
S7 times	
• Number	2 048
Retentivity	
— adjustable	Yes
IEC timer	
• Number	Any (only limited by the main memory)
Retentivity	
— adjustable	Yes
Data areas and their retentivity	
Retentive data area (incl. timers, counters, flags), max.	128 kbyte; Available retentive memory for bit memories, timers, counters, DBs, and technology data (axes): 88 KB
Flag	
• Number, max.	16 kbyte
• Number of clock memories	8; 8 clock memory bit, grouped into one clock memory byte
Data blocks	
• Retentivity adjustable	Yes

• Retentivity preset	No
Local data	
• per priority class, max.	64 kbyte; max. 16 KB per block
Address area	
Number of IO modules	1 024; max. number of modules / submodules
I/O address area	
• Inputs	32 kbyte; All inputs are in the process image
• Outputs	32 kbyte; All outputs are in the process image
per integrated IO subsystem	
— Inputs (volume)	8 kbyte
— Outputs (volume)	8 kbyte
per CM/CP	
— Inputs (volume)	8 kbyte
— Outputs (volume)	8 kbyte
Subprocess images	
• Number of subprocess images, max.	32
Address space per module	
• Address space per module, max.	288 byte; For input and output data respectively
Address space per station	
• Address space per station, max.	2 560 byte; for central inputs and outputs; depending on configuration; 2 048 bytes for ET 200SP modules + 512 bytes for ET 200AL modules
Hardware configuration	
Number of distributed IO systems	32; A distributed I/O system is characterized not only by the integration of distributed I/O via PROFINET or PROFIBUS communication modules, but also by the connection of I/O via AS-i master modules or links (e.g. IE/PB-Link)
Number of DP masters	
• Via CM	1
Number of IO Controllers	
• integrated	1
• Via CM	0
Rack	
• Modules per rack, max.	80; CPU + 64 modules + server module (mounting width max. 1 m) + 16 ET 200AL modules
• Number of lines, max.	1
PtP CM	
• Number of PtP CMs	the number of connectable PtP CMs is only limited by the number of available slots
Time of day	
Clock	
• Type	Hardware clock

• Backup time	6 wk; At 40 °C ambient temperature, typically
• Deviation per day, max.	10 s; Typ.: 2 s
Operating hours counter	
• Number	16
Clock synchronization	
• supported	Yes
• to DP, master	Yes; Via CM DP module
• to DP, slave	Yes; Via CM DP module
• in AS, master	Yes
• in AS, slave	Yes
• on Ethernet via NTP	Yes
Interfaces	
Number of PROFINET interfaces	1
Number of PROFIBUS interfaces	1; Via CM DP module
With optical interface	No
1. Interface	
Interface types	
• Number of ports	3; 1. integr. + 2. via BusAdapter
• integrated switch	Yes
• RJ 45 (Ethernet)	Yes; X1 P3; opt. X1 P1 and X1 P2 via BusAdapter BA 2x RJ45
• BusAdapter (PROFINET)	Yes; Applicable BusAdapter: BA 2x RJ45, BA 2x FC
Protocols	
• IP protocol	Yes; IPv4
• PROFINET IO Controller	Yes
• PROFINET IO Device	Yes
• SIMATIC communication	Yes
• Open IE communication	Yes
• Web server	Yes
• Media redundancy	Yes; MRP Automanager according to IEC 62439-2 Edition 2.0
PROFINET IO Controller	
Services	
— PG/OP communication	Yes
— S7 routing	Yes
— Isochronous mode	Yes
— Open IE communication	Yes
— IRT	Yes
— MRP	Yes; As MRP redundancy manager and/or MRP client; max. number of devices in the ring: 50
— MRPD	Yes; Requirement: IRT
— PROFINergy	Yes
— Prioritized startup	Yes; Max. 32 PROFINET devices

— Number of connectable IO Devices, max.	64; In total, up to 256 distributed I/O devices can be connected via AS-i, PROFIBUS or PROFINET
— Of which IO devices with IRT, max.	64
— Number of connectable IO Devices for RT, max.	64
— of which in line, max.	64
— Number of IO Devices that can be simultaneously activated/deactivated, max.	8; in total across all interfaces
— Number of IO Devices per tool, max.	8
— Updating times	The minimum value of the update time also depends on communication share set for PROFINET IO, on the number of IO devices, and on the quantity of configured user data
Update time for IRT	
— for send cycle of 250 µs	250 µs to 4 ms; Note: In the case of IRT with isochronous mode, the minimum update time of 625 µs of the isochronous OB is decisive
— for send cycle of 500 µs	500 µs to 8 ms; Note: In the case of IRT with isochronous mode, the minimum update time of 625 µs of the isochronous OB is decisive
— for send cycle of 1 ms	1 ms to 16 ms
— for send cycle of 2 ms	2 ms to 32 ms
— for send cycle of 4 ms	4 ms to 64 ms
— With IRT and parameterization of "odd" send cycles	Update time = set "odd" send clock (any multiple of 125 µs: 375 µs, 625 µs ... 3 875 µs)
Update time for RT	
— for send cycle of 250 µs	250 µs to 128 ms
— for send cycle of 500 µs	500 µs to 256 ms
— for send cycle of 1 ms	1 ms to 512 ms
— for send cycle of 2 ms	2 ms to 512 ms
— for send cycle of 4 ms	4 ms to 512 ms
PROFINET IO Device	
Services	
— PG/OP communication	Yes
— S7 routing	Yes
— Isochronous mode	No
— Open IE communication	Yes
— IRT	Yes
— MRP	Yes
— MRPD	Yes; Requirement: IRT
— PROFINergy	Yes
— Shared device	Yes
— Number of IO Controllers with shared device, max.	4

— Asset management record

Yes; Per user program

2. Interface

Interface types

- Number of ports 1
- RS 485 Yes; Via CM DP module

Protocols

- PROFIBUS DP master Yes
- PROFIBUS DP slave Yes
- SIMATIC communication Yes

Interface types

RJ 45 (Ethernet)

- 100 Mbps Yes
- Autonegotiation Yes
- Autocrossing Yes
- Industrial Ethernet status LED Yes

RS 485

- Transmission rate, max. 12 Mbit/s

Protocols

Number of connections

- Number of connections, max. 96; via integrated interfaces of the CPU and connected CPs / CMs
- Number of connections reserved for ES/HMI/web 10
- Number of connections via integrated interfaces 64
- Number of connections per CP/CM 32
- Number of S7 routing paths 16

SIMATIC communication

- S7 communication, as server Yes
- S7 communication, as client Yes
- User data per job, max. See online help (S7 communication, user data size)

Open IE communication

- TCP/IP
 - Data length, max. 64 kbyte
 - several passive connections per port, supported Yes
- ISO-on-TCP (RFC1006)
 - Data length, max. 64 kbyte
- UDP
 - Data length, max. 2 kbyte; 1 472 bytes for UDP broadcast
 - UDP multicast Yes; Max. 5 multicast circuits
- DHCP No

• SNMP	Yes
• DCP	Yes
• LLDP	Yes
Web server	
• HTTP	Yes; Standard and user pages
• HTTPS	Yes; Standard and user pages
PROFIBUS DP master	
• Number of connections, max.	48; Of which 4 each reserved for ES and HMI
Services	
— PG/OP communication	Yes
— S7 routing	Yes
— Data record routing	Yes
— Isochronous mode	No
— Equidistance	No
— Number of DP slaves	125; In total, up to 256 distributed I/O devices can be connected via AS-i, PROFIBUS or PROFINET
— Activation/deactivation of DP slaves	Yes
OPC UA	
• Runtime license required	Yes
• OPC UA Server	Yes; Data access (read, write, subscribe), method call, custom address space
— Application authentication	Yes
— Security policies	Available security policies: None, Basic128Rsa15, Basic256Rsa15, Basic256Sha256
— User authentication	"anonymous" or by user name & password
— Number of sessions, max.	32
— Number of accessible variables, max.	50 000
— Number of registerable nodes, max.	10 000
— Subscriptions per session, max.	20
— Sampling time, min.	100 ms
— Send time, min.	500 ms
— Number of server methods, max.	20
— Number of inputs/outputs per server method, max.	20
— Number of monitored items, max.	1 000; For 1 s sampling interval and 1 s send interval
— Number of server interfaces, max.	10
— Number of nodes for user-defined server interfaces, max.	1 000
Further protocols	
• MODBUS	Yes; MODBUS TCP
Media redundancy	
• Switchover time on line break, typ.	200 ms; For MRP, bumpless for MRPD

- Number of stations in the ring, max.

50

Isochronous mode

Isochronous operation (application synchronized up to terminal)

Yes; Only with PROFINET; with minimum OB 6x cycle of 625 µs

S7 message functions

Number of login stations for message functions, max.

32

Program alarms

Yes

Number of configurable program alarms

5 000

Number of simultaneously active program alarms

- Number of program alarms

300

- Number of alarms for system diagnostics

100

- Number of alarms for motion technology objects

80

Test commissioning functions

Joint commission (Team Engineering)

Yes; Parallel online access possible for up to 5 engineering systems

Status block

Yes; Up to 8 simultaneously (in total across all ES clients)

Single step

No

Number of breakpoints

8

Status/control

- Status/control variable

Yes

- Variables

Inputs/outputs, memory bits, DBs, distributed I/Os, timers, counters

- Number of variables, max.

— of which status variables, max.

200; per job

— of which control variables, max.

200; per job

Forcing

- Forcing

Yes

- Forcing, variables

Peripheral inputs/outputs

- Number of variables, max.

200

Diagnostic buffer

- present

Yes

- Number of entries, max.

1 000

— of which powerfail-proof

500

Traces

- Number of configurable Traces

4; Up to 512 KB of data per trace are possible

Interrupts/diagnostics/status information

Diagnostics indication LED

- RUN/STOP LED

Yes

- ERROR LED

Yes

- MAINT LED

Yes

- Monitoring of the supply voltage (PWR-LED)
- Connection display LINK TX/RX

Yes

Yes

Supported technology objects

Motion Control	Yes; Note: The number of axes affects the cycle time of the PLC program; selection guide via the TIA Selection Tool or SIZER
<ul style="list-style-type: none"> • Number of available Motion Control resources for technology objects (except cam disks) 	800
<ul style="list-style-type: none"> • Required Motion Control resources <ul style="list-style-type: none"> — per speed-controlled axis 	40
<ul style="list-style-type: none"> <ul style="list-style-type: none"> — per positioning axis 	80
<ul style="list-style-type: none"> <ul style="list-style-type: none"> — per synchronous axis 	160
<ul style="list-style-type: none"> <ul style="list-style-type: none"> — per external encoder 	80
<ul style="list-style-type: none"> <ul style="list-style-type: none"> — per output cam 	20
<ul style="list-style-type: none"> <ul style="list-style-type: none"> — per cam track 	160
<ul style="list-style-type: none"> <ul style="list-style-type: none"> — per probe 	40
<ul style="list-style-type: none"> • Positioning axis <ul style="list-style-type: none"> — Number of positioning axes at motion control cycle of 4 ms (typical value) 	5
<ul style="list-style-type: none"> <ul style="list-style-type: none"> — Number of positioning axes at motion control cycle of 8 ms (typical value) 	10
Controller	
<ul style="list-style-type: none"> • PID_Compact 	Yes; Universal PID controller with integrated optimization
<ul style="list-style-type: none"> • PID_3Step 	Yes; PID controller with integrated optimization for valves
<ul style="list-style-type: none"> • PID-Temp 	Yes; PID controller with integrated optimization for temperature
Counting and measuring	
<ul style="list-style-type: none"> • High-speed counter 	Yes

Ambient conditions

Ambient temperature during operation	
<ul style="list-style-type: none"> • horizontal installation, min. 	0 °C
<ul style="list-style-type: none"> • horizontal installation, max. 	60 °C
<ul style="list-style-type: none"> • vertical installation, min. 	0 °C
<ul style="list-style-type: none"> • vertical installation, max. 	50 °C
Ambient temperature during storage/transportation	
<ul style="list-style-type: none"> • min. 	-40 °C
<ul style="list-style-type: none"> • max. 	70 °C

Configuration

Programming	
Programming language	
<ul style="list-style-type: none"> — LAD 	Yes
<ul style="list-style-type: none"> — FBD 	Yes
<ul style="list-style-type: none"> — STL 	Yes

— SCL	Yes
— GRAPH	Yes
Know-how protection	
• User program protection/password protection	Yes
• Copy protection	Yes
• Block protection	Yes
Access protection	
• Protection level: Write protection	Yes
• Protection level: Read/write protection	Yes
• Protection level: Complete protection	Yes
Cycle time monitoring	
• lower limit	adjustable minimum cycle time
• upper limit	adjustable maximum cycle time
Dimensions	
Width	100 mm
Height	117 mm
Depth	75 mm
Weights	
Weight, approx.	310 g
last modified:	07/13/2018